

Great entry level unit



FR-770 Left Feed Band Sealer is suitable for sealing all types of thermoplastic materials and bags. This sealer can be used in a variety of fields such as the food, medical, and cosmetic industries. Can seal 20-30 6" poly bags / minute. Optional embossing wheel allows operator to include a message on the seal line of the bag. For printing, we recommend our HL-M810 band sealers.

Standard Features:

- Durable stainless steel construction
- Easy to operate – minimal operator training
- Fast warm up time
- Solid state digital temperature controller to maintain seal bars at proper temperature for consistent seal quality
- Fully adjustable conveyor (conveyor height and depth in relation to seal bars can be adjusted)
- Motorized rubber conveyor for speed control
- Knurled pressure rolls with variable pressure adjustment
- Sealing method – constant/direct heat accompanied with a pair each of cooling and heating blocks
- Unit feeds left to right (For right to left feed, see CBS-880)
- Spare parts includes: PC Board, PTFE belt, wheel belt, and standard type set. Additional typesets can be purchased.

Options:

- Optional embossing wheel to emboss on seal line without ink
- 2-line embossing wheel
- Stainless steel stand for horizontal model
- 15mm seal width
- Digital counter to keep track of sealed packages
- 220V Voltage

SPECIFICATIONS	
POWER	110V / 60Hz
MOTOR POWER	50W
SEALING SPEED	0-472 INCHES/MINUTE
SEAL WIDTH	8MM
TEMPERATURE RANGE	0-300°C
CONVEYOR SIZE	38" X 7"
SINGLE CONVEYOR LOAD	2.2LBS
MAX CONVEYOR LOAD	6.6LBS
BAG SIZE (FILLED)- VERTICAL UNIT	MINIMUM - 7.8" / MAXIMUM – 12"
CHARACTER SIZE	3 X 4 X 9MM
OPTIONAL EMBOSSING	1 LINE EMBOSSING (2 LINES AVAILABLE) 3 SECTIONS W/ 15 CHARACTERS/LINE
DIMENSIONS	H: 33" X 17" X 13" V: 33" X 17" X 22"
WEIGHT	H: 66-LBS V: 86-LBS



STAINLESS STEEL CONTINUOUS BAND SEALER

Model: FR-770



Circuit Breaker

Flip circuit breaker to "off" position

Embossing Knob

Adjust pressure of embossing wheel

Guide

Bag entry guide

Guide

Bag entry guide

Umbrella Gear Base

Install during initial set-up of machine

Sealing Height Knob

Adjusts sealing height on both sides of support brackets

Conveyor Height Adjustment

Adjusts height of conveyor table (10-40mm) - Horizontal Only

Power Switch



Digital Temp Controller

Fan

Heat Switch

Turns on temperature controller to activate sealing

Emergency Stop

Conveyor Speed Adjustment

8820 Baird Avenue • Northridge, CA 91324 • T: 818-718-8818 • F: 818-718-8857

✉ info@sealersales.com

🌐 www.sealersales.com