

## ADJUSTABLE SPREADER BEAM- SBM-BFB-100-6

APPROX WEIGHT: 302 lbs.

DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

\*\*\* ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE \*\*\*
ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON





## STANDARD FEATURES

MODEL NUMBER IS SBM-BFB-100-6
OVERALL WIDTH IS 6 1/2"
OVERALL LENGTH IS 80 1/2"
OVERALL HEIGHT IS 25 1/2"
MAX CAPACITY IS 10,000 LBS.
USABLE UPPER BAIL IS 4" W x 7 1/2" H
USABLE LOWER BAIL IS 3" W x 5 3/4" H
BAILS ADJUSTABLE IN 4" INCREMENTS
MAX SPREAD 72"
MIN SPREAD 24"
TOUGH BAKED IN POWDER COATED BLUE FINISH

## SPECIAL FEATURES

NONE

## DIMENSION TOLERANCE ± 1/4"

		DiiviE		02210 (1102 ± 171
I, THE UNDERSIGNED, AGREE THAT THE PRODUCT REPRESENTED SATISFIES DESIGN AND DIMENSIC REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUT CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, SO AND LOCAL REGULATIONS AND STANDARDS UNITS REQUIRING APPROVAL DRAWING MODIFIED ARE NON-RETURNABLICATION [1] As marked				MENSION MY DUTY TO ATION ERAL, STATE IDARDS. AWINGS OR NABLE
	Signed:			_Date:
Printed Name:  LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING				
				P.O.# ,
VESTIL MANUFACTURING				X W.O.# X
DRAW	<sup>'N BY:</sup> TAL	DATE: 6/9/2	021	SALES: X
REFERE	ENCE: X	SC	ALE: 1:16	FILE NAME:
QUOTI	ED LEAD TIME: X	QUOTE #		08-007-469