



# FOOT PUMP HYDRAULIC SCISSOR LIFT TABLE - SCTAB-500-2033-FP

APPROX WEIGHT: 204.37 lbs.  
DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

\*\*\* ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE \*\*\*

ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON




DIMENSION TOLERANCE  $\pm 1/4"$

## STANDARD FEATURES

MODEL NUMBER IS SCTAB-500-2033-FP  
PLATFORM WIDTH IS 20 3/8"  
PLATFORM LENGTH IS 33 3/8"  
RAISED HEIGHT IS 28"  
LOWERED HEIGHT IS 6"  
TABLE CAPACITY (EVENLY DISTRIBUTED)  
MAX CAPACITY IS 500 LBS  
SAFETY MAINTENANCE PROPS, DISPLACEMENT  
STYLE CYLINDERS INSTALLED ROD DOWN  
EMERGENCY SAFETY STOP HYDRAULIC FUSES  
TWO SPEED AUTO SHIFTING MANUAL FOOT PUMP  
NUMBER OF PUMPS TO RAISE TABLE  
LOW PRESSURE: 10  
HIGH PRESSURE: 28  
DURABLE LIQUID PAINT BLUE FINISH

## SPECIAL FEATURES

NONE



A  
P  
P  
R  
O  
V  
A  
L

I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS.

**ANY MODIFIED UNITS ARE NON-RETURNABLE**

☐ As drawn ☐ As marked

Signed: \_\_\_\_\_ Date: \_\_\_\_\_

Printed Name: \_\_\_\_\_

LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING

DISTRIBUTOR'S NAME:

VESTIL MANUFACTURING

DRAWN BY: VG

DATE: 2/15/13

REFERENCE: X

SCALE: 1:10

QUOTED LEAD TIME: X

QUOTE # X

P.O.#

X

W.O.#

X

SALES:

X

FILE NAME:

01-007-007

FOR INTERNAL USE ONLY  
PROJECT SIGN OFF

SALES

ENG.

FAB.

POWER