

Versatile – Easy to Use – Great Value

- Plug-in electronic timer for variable control
- All metal construction
- No warm-up time
- Options: sealers with sliding cutter also available
- Round wire option available for seal and cut

Our KF-series impulse hand sealers seal poly bags and other thermoplastic materials quickly and efficiently without any warm-up time. Depending on the model of the machine, material up to 20" wide and 20mil total thickness can be sealed. The sealers are equipped with a plug-in electronic timer which controls the different sealing times needed for the varying thicknesses of different materials. Available in 4", 8", 12", 16", 20" with a 2mm, 2.6mm or 5mm seal width. Cut and Seal Applications: Round wire heating elements are available for cut and seal applications. When ordering, add the letters rnd to the model number. (Example: 12" hand sealer with round cut wire – KF-300Hrnd.)



Model #	Seal Length	Seal Width	Power	Weight (lbs)
KF-100H	4"	2MM	160W	5
KF-200H*	8"	2MM	160W	6
KF-205H	8"	5MM	450W	7
KF-300H*	12"	2MM	380W	10
KF-305H	12"	5MM	640W	11
KF-400H*	16"	2.6MM	600W	11
KF-520H*	20"	2.6MM	730W	13
KF-525H	20"	5MM	900W	15

* ETL Listed

KF-series hand sealers w/ a sliding cutter allow you to seal and cut in one easy step. Available in 8", 12", 16", 20" with a 2mm, 2.6mm, 5mm, or 10mm seal width. Easy to Operate: Set the timer; insert the bag between the sealing bars, then press down and release. We recommend that the user hold the sealing arm down for an additional second or two to ensure enough time for the bag to set and cool.

Model #	Seal Length	Seal Width	Power	Weight (lbs)
KF-200HC*	8"	2MM	260W	7
KF-205HC	8"	5MM	520W	9
KF-210HC	8"	10MM	1000W	12
KF-300HC*	12"	2MM	380W	11
KF-305HC	12"	5MM	760W	13
KF-400HC*	16"	2.6MM	680W	13
KF-405HC	16"	5MM	800W	15
KF-500HC*	20"	2.6MM	730W	16
KF-505HC	20"	5MM	900W	18

* ETL Listed

