



Custom tailored to fit your needs

- Available in any length – 12”, 18”, 24”, up to 40”
- Single or double impulse sealing
- 2.7mm, 5mm, or 10mm sealing widths
- Open back frame allowing front-to-back pass thru capabilities
- Foot pedal cycle activation
- Work table included
- Pneumatically operated - quieter than automatic sealers
- Better sealing pressure vs. manual sealers
- External compressor not included - air usage requirements - 100PSI (3-5CFM)

More Details:

Our WNC2-series of pneumatic foot sealers are all custom units tailored to you.

Provide us with the following specifications:

1. Sealing Length
2. Sealing Width
3. Single or Double Impulse Sealing

Sealing and congealing time are regulated and sealing pressure is consistent every time. Manufacturer’s replacement kit includes one element and one PTFE cloth.

Stock Number	Seal Length	Seal Width	Seal Type
WNC2-305	12”	5mm	Single Impulse
WNC2-3010	12”	10mm	Single Impulse
WNC2-455	18”	5mm	Single Impulse
WNC2-4510	18”	10mm	Single Impulse
WNC2-605	24”	5mm	Single Impulse
WNC2-6010	24”	10mm	Single Impulse
WNC2-755	30”	5mm	Single Impulse
WNC2-7510	30”	10mm	Single Impulse
WNC2-305T	12”	5mm	Double Impulse
WNC2-3010T	12”	10mm	Double Impulse
WNC2-455T	18”	5mm	Double Impulse
WNC2-4510T	18”	10mm	Double Impulse
WNC2-605T	24”	5mm	Double Impulse
WNC2-6010T	24”	10mm	Double Impulse
WNC2-755T	30”	5mm	Double Impulse
WNC2-7510T	30”	10mm	Double Impulse