

# testo 160 IAQ Wi-Fi Data Logger

For monitoring temperature, humidity, atmospheric pressure and CO<sub>2</sub> concentration.

---

Wireless measurement value transfer to the testo Cloud

---

Lowest installed cost - no power wiring or communication wiring needed. Leaving more capital for PPE, Filters, cleaning services

---


Flexibility - move the data logger from unoccupied to occupied classes and offices as needed

---

Safety/Compliance - up to 10 authorized users can view CO<sub>2</sub>/RH/Temp data, complying w/ ASHRAE Guidelines

---

Internal sensors for easy and convenient set up



The easy to use testo 160 IAQ Wi-Fi Data Logger is ideal for monitoring indoor air quality. Using internal sensors for temperature, humidity, CO<sub>2</sub>, and atmospheric pressure, the testo 160 IAQ accurately determines the air quality of your desired area. The logger comes with a large internal memory that stores 40,000 measurement values, as well as a battery back up to protect your data in the event of a blackout or Wi-Fi network issues.

The testo 160 logger transfers these measurement values wirelessly to the testo Cloud.

On your testo Cloud account, you can configure multiple data loggers and set alarm points, designate authorized users, and set recipients for alarms and reports. This data is accessible at any time from any enabled device, such as a smart phone, tablet, PC or Mac. Additionally, you can preset measurement limits and, if these limits are exceeded, an alarm is immediately provided by text and/or email.

# The testo 160 Cloud

## Our packages

The testo 160 Cloud is the central operating system of the testo 160 data logger. Here, you can configure all of your Wi-Fi data loggers, set measurement limit alarms, and analyze measurement data. You must first register at [www.saveris2.net](http://www.saveris2.net) to have access to the testo 160 Cloud.

Depending on the range of functions you require, you have a choice between the free Basic version, or the more extensive Advanced version of the cloud. In both packages, you have access to an API interface in order to export measurement data to your systems.

	Basic	Advanced			
<b>Measuring cycle</b>	15 min. to 24 h	1 min. to 24 h (selectable)			
<b>Communication cycle</b>	15 min. to 24 h	1 min. to 24 h (selectable)			
<b>Data storage</b>	Max. 3 months	Max. 2 years			
<b>Reports</b>	Manual (.pdf/.csv)	Manual (.pdf/.csv) Automatic (.pdf/.csv)			
<b>Data analysis</b>	1 measurement channel	Up to 10 measurement channels simultaneously			
<b>Number of users per account</b>	1	10			
<b>Number of Wi-Fi data loggers per account</b>	Unlimited	Unlimited			
<b>Alarm options</b>	Upper/lower alarm limits	<ul style="list-style-type: none"> <li>• Upper/lower alarm limits</li> <li>• Alarm delay</li> <li>• Time control of alarms</li> </ul>			
<b>System notifications</b>	<ul style="list-style-type: none"> <li>• Low battery notification</li> <li>• Radio link interrupted</li> <li>• Power supply interrupted</li> </ul>	<ul style="list-style-type: none"> <li>• Low battery notification</li> <li>• Radio link interrupted</li> <li>• Power supply interrupted</li> </ul>			
<b>Email alarm</b>	Yes	Yes			
<b>SMS alarm</b>	No	<ul style="list-style-type: none"> <li>• Incl. 25 text msgs per logger per year</li> <li>• More SMS packages purchaseable</li> </ul>			
		<table border="1"> <tr> <td>12-month license order no. 0526 0735</td> <td>24-month license order no. 0526 0732</td> <td>36-month license order no. 0526 0733</td> </tr> </table>	12-month license order no. 0526 0735	24-month license order no. 0526 0732	36-month license order no. 0526 0733
12-month license order no. 0526 0735	24-month license order no. 0526 0732	36-month license order no. 0526 0733			

Register now: <https://americas.saveris.net/>

## Ordering data Wi-Fi data loggers

### testo 160 IAQ

testo 160 IAQ Wi-Fi Data Logger with display and integrated sensors for temperature, humidity, CO<sub>2</sub> and atmospheric pressure



Order no. 0572 2014

#### Temperature measurement

Measuring range	32 to 122 °F (0 to +50 °C)
Accuracy	± 0.9 °F (± 0.5 °C)
Resolution	0.1 °F (0.1 °C)

#### Humidity measurement

Measuring range	0 to 100 %RH (non-condensing)
Accuracy	±2 %RH at 77 °F (+25 °C) and 20 to 80 %RH ±3 %RH at 77 °F (+25 °C) and < 20 %RH and > 80 %RH ±1 %RH hysteresis ±1 %RH / year drift
Resolution	0.1% RH

#### CO<sub>2</sub> measurement

Measuring range	0 to 5,000 ppm
Accuracy	±(50 ppm + 3 % of m.v.) at 77 °F (+25 °C) Without external power supply: ±(100 ppm + 3 % of m.v.) at 77 °F (+25 °C)
Resolution	1 ppm

#### Pressure measurement

Measuring range	600 to 1100 mbar
Accuracy	±3 mbar at 71.6 °F (+22 °C)
Resolution	.40 inH2O (1 mbar)

#### WLAN

Standard	802.11 b/g/n
Security	WPA2 Enterprise: EAP-TLS, EAP-TTLS-TLS, EAP-TTLS-MSCHAPv2, EAP-TTLS-PSK, EAP-PEAP0-TLS, EAP-PEAP0-MSCHAPv2, EAP-PEAP0-PSK, EAP-PEAP1-TLS, EAP-PEAP1-MSCHAPv2, EAP-PEAP1-PSK, WPA Personal, WPA2 (AES), WPA (TKIP), WEP

#### General

Operating temperature	32 to 122 °F (0 to +50 °C)
Storage temperature	32 to 122 °F (0 to +50 °C)
Protection class	IP20
Measuring cycle	Dependent on Cloud licence Basic: 15 min to 24 h Advanced: 1 min to 24 h
Communication cycle	Dependent on Cloud licence Basic: 15 min to 24 h Advanced: 1 min to 24 h
Memory	32,000 readings (sum of all channels)
Voltage supply (alternatively, power via USB connection)	4 x AA alkaline batteries 1.5 V
Battery life (depending on the measuring and communication cycle through the Cloud)	1 year
Dimensions	4.6 x 3.23 x 1.26 in. (117 x 82 x 32 mm)
Weight (including batteries)	0.6 lbs. (269 g)

## Accessories

	Order no.
Deco-cover for testo 160 IAQ	0554 2012
Wall bracket for testo 160 IAQ	0554 2015
Alkaline AA batteries up to -14 °F (-10 °C) (pack of 4)	0515 0414
Magnetic adapter for testo Saveris 2 wall bracket	0554 2001
External USB power supply	0572 2020
ISO calibration certificate temperature -17.6 °F, 32 °F, 104 °F (-8 °C, 0 °C, +40 °C)	0520 0171
ISO calibration certificate humidity at 77 °F (+25 °C), humidity points 11.3 %RH and 75.3 %RH	0520 0076
ISO calibration certificate CO <sub>2</sub> , calibration points 0; 1000; 5000 ppm	0520 0033

