

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA
GHS

Printing date: 2/4/2021


Revision: 2/4/2021

SECTION 1: Identification of the substance/mixture and of the company/ undertaking

- **1.1 Product identifier**
- Trade name: Enzy-Out v.2
- Article number: 100347
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**
No further relevant information available.
- **Application of the substance / the mixture:** Odour neutralising agent
- **1.3 Details of the supplier of the Safety Data Sheet**
- **Manufacturer/Supplier:**
Theochem Laboratories
7373 Rowlett Park Drive
Tampa, FL 33610
Phone: 813-237-6463
- **1.4 Emergency telephone number:**
ChemTel Inc.
+1 (800)255-3924, +1 (813)248-0585



SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
 - **Classification according to Regulation (EC) No 1272/2008**
The product is not classified as hazardous according to GHS regulations.
The product is not classified as hazardous according to OSHA GHS regulations within the United States.
The product is not classified as hazardous according to the CLP regulation.
 - **2.2 Label elements**
 - **Labelling according to Regulation (EC) No 1272/2008**
The product is not classified as hazardous according to OSHA GHS regulations within the United States.
The product is not classified as hazardous according to the CLP regulation.
 - **Hazard pictograms** Not Regulated
 - **Signal word** Not Regulated
 - **Hazard-determining components of labelling:** None.
 - **Hazard statements** Not Regulated
 - **Precautionary statements** Not Regulated.
 - **NFPA ratings (scale 0 - 4)**
- | | |
|---|--|
|  | Health = 0
Fire = 0
Reactivity = 0 |
|---|--|
- **HMIS-ratings (scale 0 - 4)**
- | | | | |
|--|------------|---|----------------|
| <table border="1" style="border-collapse: collapse;"><tr><td style="background-color: #0000FF; color: white; padding: 2px;">HEALTH</td><td style="text-align: center; padding: 2px;">0</td></tr></table> | HEALTH | 0 | Health = 0 |
| HEALTH | 0 | | |
| <table border="1" style="border-collapse: collapse;"><tr><td style="background-color: #FF0000; color: white; padding: 2px;">FIRE</td><td style="text-align: center; padding: 2px;">0</td></tr></table> | FIRE | 0 | Fire = 0 |
| FIRE | 0 | | |
| <table border="1" style="border-collapse: collapse;"><tr><td style="background-color: #FFFF00; padding: 2px;">REACTIVITY</td><td style="text-align: center; padding: 2px;">0</td></tr></table> | REACTIVITY | 0 | Reactivity = 0 |
| REACTIVITY | 0 | | |

(Cont'd. on page 2)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA
GHS

Printing date: 2/4/2021

Revision: 2/4/2021

Trade name: Enzy-Out v.2

(Cont'd. from page 1)

- **2.3 Other hazards** There are no other hazards not otherwise classified that have been identified.
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

SECTION 3: Composition/information on ingredients

- **3.2 Mixtures**
- **Components:** None in reportable quantities.

SECTION 4: First aid measures

- **4.1 Description of first aid measures**
- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:**
Immediately rinse with water.
If skin irritation continues, consult a doctor.
- **After eye contact:**
Remove contact lenses if worn.
Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.
- **After swallowing:**
Rinse out mouth and then drink plenty of water.
Do not induce vomiting; call for medical help immediately.
- **4.2 Most important symptoms and effects, both acute and delayed**
Gastric or intestinal disorders.
- **4.3 Indication of any immediate medical attention and special treatment needed**
Treat skin and mucous membrane with antihistamine and corticoid preparations.

SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:**
The product is not flammable.
Use fire extinguishing methods suitable to surrounding conditions.
- **For safety reasons unsuitable extinguishing agents:** None.
- **5.2 Special hazards arising from the substance or mixture**
No further relevant information available.
- **5.3 Advice for firefighters**
- **Protective equipment:**
Wear self-contained respiratory protective device.
Wear fully protective suit.

(Cont'd. on page 3)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA
GHS

Printing date: 2/4/2021

Revision: 2/4/2021

Trade name: Enzy-Out v.2

(Cont'd. from page 2)

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**
Ensure adequate ventilation
Use personal protective equipment as required.
- **6.2 Environmental precautions** Avoid release to the environment.
- **6.3 Methods and material for containment and cleaning up**
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
Clean the affected area carefully; suitable cleaners are:
Warm water
- **6.4 Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

SECTION 7: Handling and storage

- **7.1 Precautions for safe handling**
Store in cool, dry place in tightly closed receptacles.
Use only in well ventilated areas.
Prevent formation of aerosols.
- **Information about fire - and explosion protection:** No special measures required.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** Store in a cool location.
- **Information about storage in one common storage facility:** Store away from foodstuffs.
- **Further information about storage conditions:** Keep container tightly sealed.
- **7.3 Specific end use(s)** No further relevant information available.

SECTION 8: Exposure controls/personal protection

- **8.1 Control parameters**
- **Ingredients with limit values that require monitoring at the workplace:**
The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.
- **DNELs:** No further relevant information available.
- **PNECs:** No further relevant information available.
- **8.2 Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**
The usual precautionary measures are to be adhered to when handling chemicals.
Keep away from foodstuffs, beverages and feed.
Wash hands before breaks and at the end of work.
Do not inhale gases / fumes / aerosols.

(Cont'd. on page 4)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA
GHS

Printing date: 2/4/2021

Revision: 2/4/2021

Trade name: Enzy-Out v.2

(Cont'd. from page 3)

Avoid contact with the eyes.
Avoid close or long term contact with the skin.

- **Respiratory protection:**
Not required under normal conditions of use.
For spills, respiratory protection may be advisable.
- **Protection of hands:**



Protective gloves

Gloves are advised for repeated or prolonged contact.
Wear protective gloves to handle contents of damaged or leaking units.
The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

- **For the permanent contact gloves made of the following materials are suitable:**
Nitrile rubber, NBR
Butyl rubber, BR
Neoprene gloves
- **Eye protection:**



Safety glasses

- **Body protection:** Protection may be required for spills.
- **Limitation and supervision of exposure into the environment:** No special requirements.
- **Risk management measures:** No special requirements.

SECTION 9: Physical and chemical properties

• 9.1 Information on basic physical and chemical properties

• Appearance

- | | |
|---------------------------|-----------------|
| • Form: | Liquid |
| • Colour: | White |
| • Odour: | Pleasant |
| • Odour threshold: | Not determined. |

- | | |
|---------------------------------------|-----------------|
| • pH-value: | 6.8 – 7.5 |
| • Melting point/Melting range: | Not determined. |
| • Boiling point/Boiling range: | 100 °C (212 °F) |

- | | |
|-----------------------|-----------------|
| • Flash point: | Not applicable. |
|-----------------------|-----------------|

- | | |
|---|-----------------|
| • Flammability (solid, gaseous): | Not applicable. |
|---|-----------------|

- | | |
|--|-----------------|
| • Auto/Self-ignition temperature: | Not determined. |
|--|-----------------|

- | | |
|-------------------------------------|-----------------|
| • Decomposition temperature: | Not determined. |
|-------------------------------------|-----------------|

- | | |
|-------------------------|-------------------------------|
| • Self-igniting: | Product is not self-igniting. |
|-------------------------|-------------------------------|

(Cont'd. on page 5)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA
GHS

Printing date: 2/4/2021

Revision: 2/4/2021

Trade name: Enzy-Out v.2

(Cont'd. from page 3)

· Danger of explosion:	Product does not present an explosion hazard.
· Explosion limits	
Lower:	Not determined.
Upper:	Not determined.
· Vapour pressure:	23 hPa (17 mm Hg)
· Density:	0.98 – 1.00 g/cm ³ (8.178 – 8.345 lbs/gal)
· Relative density:	Not determined.
· Vapour density:	Not determined.
· Evaporation rate:	< 1.0 (Butyl acetate = 1)
· Solubility in / Miscibility with water:	Fully miscible.
· Partition coefficient (n-octanol/water):	Not determined.
· Viscosity	
Dynamic:	2500 - 5000 cP
Kinematic:	Not determined.
· 9.2 Other information	No further relevant information available.

SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:**
No decomposition if used and stored according to specifications.
To avoid thermal decomposition do not overheat.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** Excessive heat.
- **10.5 Incompatible materials** No further relevant information available.
- **10.6 Hazardous decomposition products** Possible in traces.

SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity:** Based on available data, the classification criteria are not met.
- **LD/LC50 values relevant for classification:** None.
- **Primary irritant effect**
- **Skin corrosion/irritation:** Based on available data, the classification criteria are not met.
- **Serious eye damage/irritation:** Slight irritant effect on eyes.
- **Respiratory or skin sensitisation:** Based on available data, the classification criteria are not met.

(Cont'd. on page 6)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA
GHS

Printing date: 2/4/2021

Revision: 2/4/2021

Trade name: Enzy-Out v.2

(Cont'd. from page 3)

- **Carcinogenic categories**

- **IARC (International Agency for Research on Cancer):**

None of the ingredients are listed.

- **NTP (National Toxicology Program):**

None of the ingredients are listed.

- **OSHA-Ca (Occupational Safety & Health Administration):**

None of the ingredients are listed.

- **Probable routes of exposure:**

Eye contact.

Skin contact.

Ingestion.

- **Acute effects (acute toxicity, irritation and corrosivity):** No further relevant information available.

- **Repeated dose toxicity:** No further relevant information available.

- **Germ cell mutagenicity:** Based on available data, the classification criteria are not met.

- **Carcinogenicity:** Based on available data, the classification criteria are not met.

- **Reproductive toxicity:** Based on available data, the classification criteria are not met.

- **STOT-single exposure:** Based on available data, the classification criteria are not met.

- **STOT-repeated exposure:** Based on available data, the classification criteria are not met.

- **Aspiration hazard:** Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

- **12.1 Toxicity**

- **Aquatic toxicity:** The product contains materials that are harmful to the environment.

- **12.2 Persistence and degradability** Biodegradable

- **12.3 Bioaccumulative potential** No further relevant information available.

- **12.4 Mobility in soil** No further relevant information available.

- **Additional ecological information:**

- **General notes:**

Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

- **12.5 Results of PBT and vPvB assessment**

- **PBT:** Not applicable.

- **vPvB:** Not applicable.

- **12.6 Other adverse effects** No further relevant information available.

SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**

- **Recommendation**

Smaller quantities can be disposed of with household waste.

(Cont'd. on page 7)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA
GHS

Printing date: 2/4/2021

Revision: 2/4/2021

Trade name: Enzy-Out v.2

(Cont'd. from page 6)

Small amounts may be diluted with plenty of water and washed away. Dispose of larger amounts in accordance with Local Authority requirements.

The user of this material has the responsibility to dispose of unused material, residues and containers in compliance with all relevant local, state and federal laws and regulations regarding treatment, storage and disposal for hazardous and nonhazardous wastes.

- **Uncleaned packaging:**
- **Recommendation:** Disposal must be made according to official regulations.
- **Recommended cleansing agents:** Water, if necessary together with cleansing agents.

SECTION 14: Transport information

- | | |
|--|-----------------|
| · 14.1 UN-Number | |
| · DOT, ADR, IMDG, IATA | Not Regulated |
| · 14.2 UN proper shipping name | |
| · DOT, ADR, IMDG, IATA | Not Regulated |
| · 14.3 Transport hazard class(es) | |
| · DOT, ADR, IMDG, IATA | |
| · Class | Not Regulated |
| · 14.4 Packing group | |
| · DOT, ADR, IMDG, IATA | Not Regulated |
| · 14.5 Environmental hazards: | |
| · Marine pollutant: | No |
| · 14.6 Special precautions for user | Not applicable. |
| · 14.7 Transport in bulk according to Annex II of Marpol and the IBC Code | Not applicable. |

SECTION 15: Regulatory information

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**
 - **United States (USA)**
 - **SARA**
- | | |
|--|-------------------------------------|
| · Section 355 (extremely hazardous substances): | |
| | None of the ingredients are listed. |
| · Section 313 (Specific toxic chemical listings): | |
| | None of the ingredients are listed. |
| · TSCA (Toxic Substances Control Act): | |
| | All ingredients are listed. |

(Cont'd. on page 8)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA
GHS

Printing date: 2/4/2021

Revision: 2/4/2021

Trade name: Enzy-Out v.2

(Cont'd. from page 7)

- **Proposition 65 (California):**

- **Chemicals known to cause cancer:**

None of the ingredients are listed.

- **Chemicals known to cause reproductive toxicity for females:**

None of the ingredients are listed.

- **Chemicals known to cause reproductive toxicity for males:**

None of the ingredients are listed.

- **Chemicals known to cause developmental toxicity:**

None of the ingredients are listed.

- **Carcinogenic Categories**

- **EPA (Environmental Protection Agency)**

None of the ingredients are listed.

- **IARC (International Agency for Research on Cancer)**

None of the ingredients are listed.

- **NIOSH-Ca (National Institute for Occupational Safety and Health)**

None of the ingredients are listed.

- **Canada**

- **Canadian Domestic Substances List (DSL)**

All ingredients are listed.

- **Other regulations, limitations and prohibitive regulations**

- **Substances of very high concern (SVHC) according to REACH, Article 57**

None of the ingredients are listed.

- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Abbreviations and acronyms:**

ADR: European Agreement concerning the International Carriage of Dangerous Goods by Road

IMDG: International Maritime Code for Dangerous Goods

DOT: US Department of Transportation

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

ACGIH: American Conference of Governmental Industrial Hygienists

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

NFPA: National Fire Protection Association (USA)

HMIS: Hazardous Materials Identification System (USA)

WHMIS: Workplace Hazardous Materials Information System (Canada)

DNEL: Derived No-Effect Level (REACH)

PNEC: Predicted No-Effect Concentration (REACH)

(Cont'd. on page 9)

Safety Data Sheet
according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA
GHS

Printing date: 2/4/2021

Revision: 2/4/2021

Trade name: Enzy-Out v.2

(Cont'd. from page 8)

· SourcesWebsite, European Chemicals Agency (echa.europa.eu)Website, US EPA Substance Registry Services (ofmpub.epa.gov/sorinternet/registry/substreg/home/overview/home.do)Website, Chemical Abstracts Registry, American Chemical Society (www.cas.org)

Patty's Industrial Hygiene, 6th ed., Rose, Vernon, ed. ISBN: ISBN: 978-0-470-07488-6

Casarett and Doull's Toxicology: The Basic Science of Poisons, 8th Ed., Klaasen, Curtis D., ed., ISBN: 978-0-07-176923-5.

Safety Data Sheets, Individual Manufacturers

SDS Prepared by:

ChemTel Inc.

1305 North Florida Avenue

Tampa, Florida USA 33602-2902

Toll Free North America 1-888-255-3924 Intl. +01 813-248-0573

Website: www.chemtelinc.com