



Lined Bottom, Sides, and Lid with 8 Mesh x .047" Woven Wire (.078" Openings, 39% Open Area)

UNLESS OTHERWISE SPECIFIED:
 DIMENSIONS ARE IN INCHES
 TOLERANCES:
 FRACTIONAL $\pm 1/16$ "
 ANGULAR: ± 5 DEG.
 TWO PLACE DECIMAL ± 0.03
 THREE PLACE DECIMAL ± 0.015

Rectangular Wire Mesh Basket:
 10Lx6Wx6H, 304 SS, 3/16 Rod Frame,
 Hinged Lid with Latch, Stacking Handles,
 Mesh: 8 x .047

EST WGT
 4.3 lbs.
 MATERIAL
 304 Stainless Steel
 FINISH
 Natural

SIZE **B** DWG. NO.
 TMT-100060060-Q08S

PROPRIETARY AND CONFIDENTIAL
 THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF THREE M TOOL. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF THREE M TOOL IS PROHIBITED.

DO NOT SCALE DRAWING

SCALE: 1:4

SHEET 1 OF 1