



Lined Bottom and Sides with  
2 Mesh x .063" Welded Wire  
(.437" Openings, 76% Open Area)

UNLESS OTHERWISE SPECIFIED:  
DIMENSIONS ARE IN INCHES  
TOLERANCES:  
FRACTIONAL ± 1/16"  
ANGULAR: ± 5 DEG.  
TWO PLACE DECIMAL ±0.03  
THREE PLACE DECIMAL ±0.015

**Rectangular Wire Mesh Basket:**  
18Lx18Wx6H, 304 SS, 5/16 Rod Frame,  
Stacking Handles, Mesh: 2 x .063

**PROPRIETARY AND CONFIDENTIAL**

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF THREE M TOOL. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF THREE M TOOL IS PROHIBITED.

EST WGT  
10.1 lbs.  
MATERIAL  
304 Stainless Steel  
FINISH  
Natural

SIZE **B** DWG. NO.  
TMT-180180060-A02S

DO NOT SCALE DRAWING

SCALE: 1:6

SHEET 1 OF 1