







1/4" #18 Flattened Expanded Metal
(0.08" x 0.66" Diamond Openings
28% Open Area)



J-Channels to cover and support top edges of expanded metal




– 1-Piece Expanded Metal Body Panel, with Folded Tabs to close and support corners



Ø $\frac{3}{16}$ "
Cross
Supports

— $\varnothing \frac{5}{16}$ "
Handles and
Frame Runners



— Lined Bottom and Sides with
1/4" #18 Flattened Expanded Metal
(0.08" x 0.66" Diamond Openings
28% Open Area)

UNLESS OTHERWISE SPECIFIED:

DIMENSIONS ARE IN INCHES
TOLERANCES:
FRACTIONAL $\pm 1/16"$
ANGULAR: ± 5 DEG.
TWO PLACE DECIMAL ± 0.03
THREE PLACE DECIMAL ± 0.015

EST WGT

5.9 lbs.
MATERIAL
304 Stainless Steel

FINISH
Natural

DO NOT SCALE DRAWING

Stacking Tote Basket, 16 x 10 x 4-1/2, 304 Stainless Steel

SIZE
B

DWG. NO.

TOTE-161005-E14-SS

SCALE: 1:4

SHEET 1 OF 1