

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0015916142

Status:

Active

Overview:

C-Grid Connector Products

Description:

2.54mm Pitch C-Grid Breakaway Header, Surface Mount, Dual Row, Vertical, 14 Circuits, 0.38µm Gold (Au) Selective Plating, without PCB Locator Pegs, Tape and Reel



Series image - Reference only

Documents:	
Drawing (PDF)	Application Specification 713080001-AS-000 (PDF)
3D Model	Packaging Specification 713080000-PK-000 (PDF)
3D Model (PDF)	Packaging Specification 713080001-PK-000 (PDF)
Product Specification PS-71308-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	PCB Headers
Series	71308
Application	Board-to-Board, Signal, Wire-to-Board
Overview	C-Grid Connector Products
Product Name	C-Grid
Taxonomy	PCB Headers and Receptacles
UPC	800756040165
Physical	
Breakaway	Yes
Circuits (Loaded)	14
Circuits (maximum)	14
Color - Resin	Black
Durability (mating cycles max)	50
Flammability	94V-0
Glow-Wire Capable	No
Lock to Mating Part	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	0.843/g
Number of Rows	2
Orientation	Vertical
PCB Locator	No
PCB Retention	None
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	2.54mm
Plating min - Mating	0.381µm
Plating min - Termination	2.032µm
Polarized to Mating Part	No
Polarized to PCB	No
Robotic Placement	Pick and Place Cap
Shrouded	No
Stackable	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount

Electrical

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

71308 Series

Mates With

C-Grid Surface Mount Right-Angle PCB Receptacle [71979](#) . C-Grid Surface Mount Vertical PCB Receptacle [71395](#) . C-Grid Through-hole Vertical PCB Receptacle [71850](#) . C-Grid Shunt Terminal Housing [7859](#)

Current - Maximum per Contact	3.0A
Voltage - Maximum	250V
Solder Process Data	
Lead-freeProcess Capability	REFLOW
Process Temperature max. C	260
Material Info	
Engineering Number	71308-1614
Reference - Drawing Numbers	
Application Specification	713080001-AS-000
Packaging Specification	713080000-PK-000, 713080001-PK-000
Product Specification	PS-71308-001
Sales Drawing	713080000-SD-000

This document was generated on 10/31/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION