# NEWPORT BRASS

#### **Features**

- Solid brass construction
- Brass valve bodies
- Quarter-turn washerless ceramic disc valve cartridges
- ADA compliant traditional cross handles
- Spout assembly with integral supply hoses
- Pop-up drain with tailpiece
- 6-3/4" (17.1 cm) spout height at outlet
- 5-13/16" (14.8 cm) spout reach (c-c)
- For 8" (20.3 cm) centers Maximum 20" (50.8 cm)
- 1.2 gallons (4.5 liters) per minute maximum flow rate

## **Codes / Standards Compliance**

Meets or exceeds the following at date of manufacture:

- ASME A112.18.1/CSA B125.1
- IAPMO/cUPC
- NSF 61
- ADA
- ICC/ANSI A117.1
- Energy Policy Act of 1992
- All applicable US Federal and State material regulations



### **Widespread Lavatory Faucet**

2060





#### **Colors / Finishes**

- 10B: Oil Rubbed Bronze
- 15: Polished Nickel
- 15S: Satin Nickel PVD
- 26: Polished Chrome

• Other: Refer to the Newport Brass catalog for additional color/finish options.

#### **Specified Model**


Model	Description	Colors   Finishes
2060	Widspread Lavatory Faucet	□ 10B □ 15 □ 15S □ 26 □ Other

#### **Product Specification** Add "Color / Finish" suffix to Model number, below.

The two-handle Widespread Lavatory Faucet shall be made of solid brass construction. Faucet shall incorporate a spout assembly with integral supply hoses and feature brass valve bodies with quarter-turn washerless ceramic disc valve cartridges. Faucet shall have a 1.2 gallon (4.5 liter) per minute maximum flow rate. Product shall be for 8" (20.3 cm) centers - Maximum 20" (50.8 cm). Product shall incorporate a 6-3/4" (17.1 cm) spout height at outlet and a 5-13/16" (14.8 cm) spout reach (c-c). Faucet shall include a pop-up drain with tailpiece and incorporate ADA compliant traditional cross handles. Widespread Lavatory Faucet shall be Newport Brass Model 2060/\_\_\_\_\_.

# 2060

### **PRODUCT DIMENSIONS** (Units are in inches)



# Secant Widespread Lavatory Faucet 2060



t: 949.417.5207 | www.newportbrass.com ©2017 Brasstech, Inc.

Page 2 of 2 Spec\_2060