



600A True-RMS Dual Display Clamp Meter



Functions

- 600A AC/DC
- 1000V DC
- 750V AC
- 2000 μ A AC/DC
- 60M Ω Resistance
- Capacitance: 6000 μ F
- Differential Temperature: -328° to 2462°F
- Frequency/Duty Cycle
- Audible Continuity
- Diode Test
- Non-Contact Voltage Detection
- LRA Inrush
- Low Z (impedance)

Features

- TRMS
- Backlit Dual Display and Worklight
- Min/Max/Avg/Hold
- Peak Hold
- Auto Volts & Amp selection
- Built-in Magnet w/ hanging strap
- Test Lead Storage
- Visible high-voltage alert
- Easy access battery cover latches
- Over-molded grip
- Auto and Manual ranging
- Input Jack Lock
- Auto calibration
- Auto Power Off
- Low Battery Indicator
- 2-Year limited warranty

BACKED BY



1
YEAR
WARRANTY



Application

- Circuits in molex plugs, and diode malfunctions. Measure capacitance, voltage, microamps, circuit continuity, resistance, and temperature via K-Type thermocouples
- Flame sensing
- Check system boards and live wires



Includes

- Pipe Clamp Adapters 2 (ATTPC4)
- Silicone Test Leads (ATL58)
- Back Probes (APB3)
- Alligator Clips (AAC3)
- Temperature Probes 2 (ATT29)
- Zippered Pouch
- Batteries 4 (AAA)
- Manual



Specifications

AC Amps Measurement - Jaw Input

Range	Resolution	Accuracy	Overload Protection
60.00A	0.01A	±2.0% +8dpts	600V RMS
600.0A	0.1A	±2.0% +8dpts	

45 to 400Hz TRMS
Minimum Current for Camp Measurement 0.3A

DC Amps Measurement - Jaw Input

Range	Resolution	Accuracy	Overload Protection
60.00A	0.01A	±2.0% +8dpts	600V RMS
600.0A	0.1A	±2.0% +8dpts	

Minimum Current for Camp Measurement 0.2A

AC Microamps Measurement- Test Lead input

Range	Resolution	Accuracy	Overload Protection
600μA	0.1μA	±1.5% +3 dpts	600V RMS
2000μA	1μA		

45 to 400Hz TRMS

DC Microamps Measurement- Test Lead input

Range	Resolution	Accuracy	Overload Protection
600μA	0.1μA	±1.5% +2 dpts	600V RMS
2000μA	1μA		

AC Volts Measurement

Range	Resolution	Accuracy	Overload Protection
600.0mV	0.1mV	±1.0% +3 dpts	1000V RMS
6.000V	0.001V		
60.00V	0.01V		
600.0V	0.1V		
750V	1V		

45 to 400Hz TRMS

DC Volts Measurement

Range	Resolution	Accuracy	Overload Protection
600.0mV	0.1mV	±0.5% +4 dgts	1000V RMS
6.000V	0.001V		
60.00V	0.01V		
600.0V	0.1V		
1000V	1V	±0.8% +5 dgts	

Ohms Measurement

Range	Resolution	Accuracy	Overload Protection
600.0Ω	0.1Ω	±0.8 +3 dgts	600V RMS
6.000kΩ	0.001kΩ		
60.00kΩ	0.01kΩ		
600.0kΩ	0.1kΩ		
6.000MΩ	0.001MΩ	±1.2% +3 dgts	
60.00MΩ	0.01MΩ		

Capacitance Measurement

Range	Resolution	Accuracy	Overload Protection
10.00nF	0.01nF	3.0% +5 dpts	600V RMS
100.0nF	0.1nF		
1.000μF	0.001μF		
10.00μF	0.01μF		
100.0μF	0.1μF		
2000μF	1μF		

WARNING to avoid damaging the meter or equipment under test, safely discharge Capacitors before measuring capacitance. Large value capacitors should be discharged through appropriate resistance load. Use the DC Voltage to confirm capacitor discharge.

Diode Test Measurement

Range	Resolution	Accuracy	Overload Protection
3.0V	<3.2V DC	0.25mA	600V RMS

Temperature Measurement

Range	Resolution	Accuracy	Overload Protection
-328° to 999°F (-200° to 999°C)	0.1°F (0.1°C)	±1.0% +3.6°F (±1.0% +2.0°C)	30V RMS
1000° to 2462°F (1000° to 1350°C)	1°F (1°C)	±1.0% +3°F (±1.0% +2°C)	

Frequency Measurement - Test lead input

Range	Resolution	Accuracy	Overload Protection
99.99Hz	0.01Hz	±0.1% +3 dpts	1000V RMS
999.9Hz	0.1Hz		
9.999kHz	0.001kHz		
99.99kHz	0.01kHz		

Duty Cycle

Range	Accuracy	Overload Protection
1.0to 99.0%	±(2.0% per kHz +0.1% +5 dpts)	1000V RMS

Audible Continuity Measurement

Open Circuit Voltage <1.0V	Overload Protection
Threshold <40Ω	600V RMS

Downloads



Manual



Data Sheet



Made in KOREA