

Revision Date 17-May-2018
Version 7

1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

GHS product identifier : Synthetic CD50 Manual Transmission Fluid SAE 50
Code : 213
Product type : Liquid.

Identified uses

Lubrication oil. Not to be misted.

Details of the supplier of the safety data sheet

Manufacturer Address : U.S. Lubricants, A Division of U.S. Venture, Inc.
425 Better Way
Appleton, WI 54915

Emergency telephone number

Company Phone Number 800-490-4900
24 Hour Emergency Phone Number 800-424-9300 (CHEMTREC 705487)

2. HAZARDS IDENTIFICATION

OSHA/HCS status : This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

Classification of the substance or mixture : EYE IRRITATION – Category 2B
AQUATIC HAZARD (LONG-TERM) - Category 4

GHS label elements

Hazard pictograms : Warning
Signal word : Causes eye irritation.
Hazard statements : May cause long lasting harmful effects to aquatic life.

Precautionary statements

Prevention : Avoid release to the environment.
Wash hands thoroughly after handling.

Response : IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical attention.

Storage : Not applicable.

Disposal : Dispose of contents and container in accordance with all local, regional, national and international regulations.

Hazards not otherwise classified : None known.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance/mixture : Mixture
Other means of identification : Not available.

CAS number/other identifiers

CAS number : Not applicable.
Product code : 213

United States

Ingredient name	%	CAS number
1-Propene, 2-methyl-, homopolymer	25 - 40	9003-27-4
2,6-di-tert-Butylphenol	0.1 - 1	128-39-2

Any concentration shown as a range is to protect confidentiality or is due to batch variation.

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment and hence require reporting in this section.

Occupational exposure limits, if available, are listed in Section 8.

4. FIRST AID MEASURES

Description of necessary first aid measures

- Eye contact** : Immediately flush eyes with plenty of water, occasionally lifting the upper and lower eyelids. Check for and remove any contact lenses. Continue to rinse for at least 20 minutes. If irritation persists, get medical attention.

- Inhalation** : Remove victim to fresh air and keep at rest in a position comfortable for breathing. If not breathing, if breathing is irregular or if respiratory arrest occurs, provide artificial respiration or oxygen by trained personnel. It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation. Get medical attention if adverse health effects persist or are severe. If unconscious, place in recovery position and get medical attention immediately. Maintain an open airway. Loosen tight clothing as a collar, tie, belt or waistband.

- Skin contact** : Flush contaminated skin with plenty of water. Remove contaminated clothing and shoes. Get medical attention if symptoms occur. Wash clothing before reuse. Clean shoes thoroughly before reuse.

- Ingestion** : Wash out mouth with water. Remove dentures if any. Remove victim to fresh air and keep at rest in a position comfortable for breathing. If material has been swallowed and the exposed person is conscious, give small quantities of water to drink. Stop if the exposed person feels sick as vomiting may be dangerous. Do not induce vomiting unless directed to do so by medical personnel. If vomiting occurs, the head should be kept low so that vomit does not enter the lungs. Never give anything by mouth to an unconscious person. If unconscious, place in recovery position and get medical attention immediately. Maintain an open airway. Loosen tight clothing such as a collar, tie, belt or waistband.

Most important symptoms/effects, acute and delayed

Potential acute health effects

- Eye contact** : Causes eye irritation
- Inhalation** : No known significant effects or critical hazards.
- Skin contact** : No known significant effects or critical hazards.
- Ingestion** : No known significant effects or critical hazards.

Over-exposure signs/symptoms

- Eye contact** : Adverse symptoms may include the following:
 pain or irritation
 watering
 redness
- Inhalation** : No known significant effects or critical hazards.
- Skin contact** : No known significant effects or critical hazards.
- Ingestion** : No known significant effects or critical hazards.

Indication of immediate medical attention and special treatment needed, if necessary

- Notes to physician** : Treat symptomatically. Contact poison treatment specialist immediately if large quantities have been ingested or inhaled.
- Specific treatments** : No specific treatment.
- Protection of first-aiders** : No action shall be taken involving any personal risk or without suitable training. It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation.
- See toxicological information (Section 11)**

5. FIRE-FIGHTING MEASURES**Extinguishing media**

- Suitable extinguishing media** : Use an extinguishing agent suitable for the surrounding fire.

Unsuitable extinguishing media

- : None known.

Specific hazards arising from the chemical

- : In a fire or if heated, a pressure increase will occur and the container may burst. This material may cause long lasting harmful effects to aquatic life. Fire water contaminated with this material must be contained and prevented from being discharged to any waterway, sewer or drain.

Hazardous thermal decomposition products

- : Decomposition products may include the following materials:
Carbon dioxide
Carbon monoxide

Special protective actions for fire-fighters

- : Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire. No action shall be taken involving any personal risk or without suitable training.

Special protective equipment for fire-fighters

- : Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode.

6. ACCIDENTAL RELEASE MEASURES**Personal precautions, protective equipment and emergency procedures****For non-emergency personnel**

- : No action shall be taken involving any personal risk or without suitable training. Evacuate surrounding areas. Keep unnecessary and unprotected personnel from entering. Do not touch or walk through spilled material. Avoid breathing vapor or mist. Provide adequate ventilation. Wear appropriate respirator when ventilation is inadequate. Put on appropriate personal protective equipment.

For emergency responders

- : If specialized clothing is required to deal with the spillage, take note of any information in Section 8 on suitable and unsuitable materials. See also the information in "For nonemergency personnel".

Environmental precautions

- : Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air). Water polluting material. May be harmful to the environment if released in large quantities.

Methods and materials for containment and cleaning up**Spill**

- : Stop leak if without risk. Move containers from spill area. Approach release from upwind. Prevent entry into sewers, water courses, basements or confined areas. Wash spillages into an effluent treatment plant or proceed as follows. Contain and collect spillage with non-combustible, absorbent material e.g. sand, earth, vermiculite or diatomaceous earth and place in container for disposal according to local regulations (see Section 13). Dispose via a licensed waste disposal contractor. Contaminated absorbent material may pose the same hazard as the spilled product. Note: see Section 1 for emergency contact information and Section 13 for waste disposal.

7. HANDLING AND STORAGE

Precautions for safe handling

Protective measures : Put on appropriate personal protective equipment (see Section 8). Do not ingest. Avoid contact with eyes, skin and clothing. Avoid breathing vapor or mist. Keep in the original container or an approved alternative made from a compatible material, kept tightly closed when not in use. Empty containers retain product residue and can be hazardous. Avoid contact with used product. Do not reuse container.

Advice on general occupational hygiene : Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking. Remove Contaminated clothing and protective equipment before entering eating areas. See also Section 8 for additional information on hygiene measures.

Conditions for safe storage, including any incompatibilities : Store in accordance with local regulations. Store in original container protected from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see Section 10) and food and drink. Keep container tightly closed and sealed until ready for use. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Do not store in unlabeled containers. Use appropriate containment to avoid environmental contamination.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Occupational exposure limits

Under conditions which may generate mists, the following exposure limits are recommended:
 ACGIH TLV TWA: 5 mg/m³; STEL: 10 mg/m³.

United States

None.

Canada

None.

Appropriate engineering controls : Good general ventilation should be sufficient to control worker exposure to airborne contaminants.

Environmental exposure controls : Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation.

Individual protection measures

Hygiene measures : Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period.

Appropriate techniques should be used to remove potentially contaminated clothing. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location.

Eye/face protection : Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary to avoid exposure to liquid splashes, mists, gases or dusts. If contact is possible, the following protection should be worn, unless the assessment indicates a higher degree of protection: chemical splash goggles.

Skin protection

Hand protection : Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

- Body protection** : Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.
- Other skin protection** : Appropriate footwear and any additional skin protection measures should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.
- Respiratory protection** : Based on the hazard and potential for exposure, select a respirator that meets the appropriate standard or certification. Respirators must be used according to a respiratory protection program to ensure proper fitting, training, and other important aspects of use.

9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance

- Physical state** : Liquid.
- Color** : Red.
- Odor** : Mild/Hydrocarbon.
- Odor threshold** : Not available.
- pH** : Not available.
- Melting point / Pour point** : -38°C (-36.4°F)
- Boiling point** : Not available.
- Flash point** : Open cup: 210°C (410°F) [Cleveland.]
- Evaporation rate** : Not available.
- Flammability (solid, gas)** : Not available.
- Lower and upper explosive (flammable) limits** : Not available.
- Vapor pressure** : Not available.
- Vapor density** : Not available.
- Relative density** : 0.8665
- Solubility** : Not available.
- Partition coefficient: n-octanol/ water** : Not available.
- Auto-ignition temperature** : Not available.
- Decomposition temperature** : Not available.
- Viscosity** : Kinematic: 0.184 cm²/s (18.4 cSt) (100°C)
Kinematic: 1.175 cm²/s (117.5 cSt) (40°C)
- Volatility** : Not available
- VOC (w/w)** : Not available

10. STABILITY AND REACTIVITY

- Reactivity** : No specific test data related to reactivity available for this product or its ingredients.
- Chemical stability** : The product is stable.
- Possibility of hazardous reactions** : Under normal conditions of storage and use, hazardous reactions will not occur.
- Conditions to avoid** : No specific data.
- Incompatible materials** : Reactive or incompatible with the following materials: oxidizing materials.
- Hazardous decomposition products** : Under normal conditions of storage and use, hazardous decomposition products should not be produced.

11. TOXICOLOGICAL INFORMATION

Information on toxicological effects

There is no data available.

Acute toxicity

Product/Ingredient Name	Result	Species	Dose	Exposure
2,6-di-tert-Butylphenol	LD50 Dermal	Rabbit	>10 g/kg	-
	LD50 Oral	Rat	>5000 mg/kg	-

Irritation/Corrosion

Product/Ingredient Name	Result	Species	Score	Exposure	Observation
2,6-di-tert-Butylphenol	Skin – Moderate irritant	Rat	-	0.5 mL	-

Sensitization

There is no data available.

Carcinogenicity

There is no data available.

Specific target organ toxicity (single exposure)

There is no data available.

Specific target organ toxicity (repeated exposure)

There is no data available.

Aspiration hazard

There is no data available

Information on the likely routes of exposure : Dermal contact. Eye contact. Inhalation. Ingestion.

Potential acute health effects

Eye contact : Causes eye irritation.
Inhalation : No known significant effects or critical hazards.
Skin contact : No known significant effects or critical hazards.
Ingestion : No known significant effects or critical hazards.

Symptoms related to the physical, chemical and toxicological characteristics

Eye contact : Adverse symptoms may include the following:
 pain or irritation
 watering
 redness
Inhalation : No known significant effects or critical hazards.
Skin contact : No known significant effects or critical hazards.
Ingestion : No known significant effects or critical hazards.

Delayed and immediate effects and also chronic effects from short and long term exposure

Short term exposure

Potential immediate effects : No known significant effects or critical hazards.
Potential delayed effects : No known significant effects or critical hazards.

Long term exposure

Potential immediate effects : No known significant effects or critical hazards.
Potential delayed effects : No known significant effects or critical hazards.

Potential chronic health effects

General : No known significant effects or critical hazards.
Carcinogenicity : No known significant effects or critical hazards.
Mutagenicity : No known significant effects or critical hazards.

Teratogenicity : No known significant effects or critical hazards.
Developmental effects : No known significant effects or critical hazards.
Fertility effects : No known significant effects or critical hazards.

Numerical measures of toxicity

Acute toxicity estimates

There is no data available.

12. ECOLOGICAL INFORMATION

Toxicity

Product/ingredient name	Result	Species	Exposure
1-Propene, 2-methyl-, homopolymer	Acute LC50>5600000 µg/l Fresh Water	Fish – Oncorhynchus mykiss	96 hr

Persistence and degradability

There is no data available.

Bioaccumulative potential

Product/ingredient name	LogP _{ow}	BCF	Potential
2,6-di-tert-Butylphenol	4.5	-	High

Mobility in soil

Soil/water partition coefficient (K_{oc}) : There is no data available.
Other adverse effects : No known significant effects or critical hazards.

13. DISPOSAL CONSIDERATIONS

Disposal methods : The generation of waste should be avoided or minimized wherever possible. Disposal of this product, solutions and any by-products should comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of all authorities with jurisdiction. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible. This material and its container must be disposed of in a safe way. Care should be taken when handling empty containers that have not been cleaned or rinsed out. Empty containers or liners may retain some product residues. Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers.

14. TRANSPORT INFORMATION

	DOT	TDG	IMDG	IATA
UN number	Not regulated.	Not regulated	Not regulated.	Not regulated.
UN proper shipping name	-	-	-	-
Transport hazard class(es)	-	-	-	-
Packing group	-	-	-	-
Environmental hazards	No.	No.	No.	No.
Additional information	-	-	-	-

AERG: Not applicable.

Special precautions for user : **Transport within user's premises:** always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage.

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code : Not available.

15. REGULATORY INFORMATION

- U.S. Federal regulations** : **United States inventory TSCA 8(b)**: All components are listed or exempted.
Clean Water Act (CWA) 307: Phenol, Ethylbenzene, Benzene, Naphthalene
Clean Water Act (CWA) 311: Phenol, Ethylbenzene, Benzene, Naphthalene, Xylene.
- Clean Air Act Section 112 (b) Hazardous Air Pollutants (HAPs)** : Listed
- Clean Air Act Section 602 Class I Substances** : Not listed
- Clean Air Act Section 602 Class II Substances** : Not listed
- DEA List I Chemicals (Precursor Chemicals)** : Not listed
- DEA List II Chemicals (Essential Chemicals)** : Not listed

SARA 302/304
Composition/information on ingredients

Name	EHS	Sara 302 TPQ		SARA 304 RQ	
		(lbs)	(gallons)	(lbs)	(gallons)
Phenol	Yes.	500 / 10000	-	1000	-
Ethylene oxide	Yes.	1000	-	10	-

SARA 304 RQ : 15748031.5 lbs / 7149606.3 kg [2159778.3 gal / 8175650.4 L]

SARA 311/312
Classification : Immediate (acute) health hazard

Name	Fire hazard	Sudden release of pressure	Reactive	Immediate (acute) health hazard	Delayed (chronic) health hazard
1-Propene, 2-methyl-, homopolymer 2,6-di-tert-Butylphenol	No. No.	No. No.	No. No.	Yes. Yes.	No. No.

SARA 313
 No products were found

- State regulations**
- Massachusetts** : None of the components are listed.
 - New York** : None of the components are listed.
 - New Jersey** : None of the components are listed.
 - Pennsylvania** : None of the components are listed.

California Prop. 65

WARNING: This product contains less than 0.1% of a chemical known to the State of California to cause cancer.
WARNING: This product contains less than 1% of a chemical known to the State of California to cause birth defects or other reproductive harm.

Ingredient name	Cancer	Reproductive	No significant risk level	Maximum acceptable dosage level
Ethylbenzene	Yes.	No.	41 µg/day (ingestion) 54 µg/day (inhalation)	No.
Ethylene oxide	Yes.	Yes.	Yes.	Yes.
2-Propenoic acid, ethyl ester	Yes.	Yes.	No.	No.
Ethyl acrylate	Yes.	No.	No.	No.
Benzene	Yes.	Yes.	6.4 µg/day (ingestion) 13 µg/day (inhalation)	24 µg/day (ingestion) 49 µg/day (inhalation)
Naphthalene	Yes.	No.	Yes.	No.

Canada**Canadian Lists**

- Canada Inventory** : All components are listed or exempt.
Canadian NPRI : None of the components are listed.
CEPA Toxic substances : None of the components are listed.

16. OTHER INFORMATION**History**

- Date of issue mm/dd/yyyy** : 5/17/2018
Date of previous issue : 6/30/2015
Version : 7
Prepared by : US Lubricants

Notice to reader

To the best of our knowledge, the information contained herein is accurate. However, neither the above-named supplier, nor any of its subsidiaries, assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.

End of Safety Data Sheet