

SAFETY DATA SHEET



PROSOCO
Revision Number 2.01

Issuing Date 17-Oct-2014

Revision date 29-Aug-2018

1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

Product identifier

Product Name PROSOCO R-Guard® Cat 5® Rain Screen

Other means of identification

Product Code(s) 70435

Recommended use of the chemical and restrictions on use

Recommended use Restricted to professional users.

Uses advised against No information available

Details of the supplier of the safety data sheet

Manufacturer Address

PROSOCO, Inc.
3741 Greenway Circle
Lawrence, Kansas 66046

Emergency telephone number

8:00 AM – 5:00 PM CST Monday-Friday 785-865-4200
NON-BUSINESS HOURS (INFOTRAC) 800-535-5053

2. HAZARDS IDENTIFICATION

Classification

Reproductive toxicity	Category 1B
-----------------------	-------------

Label elements

Emergency Overview

Danger

Hazard statements

May damage fertility or the unborn child



Appearance viscous

Physical state Liquid

Odor Mild

Precautionary Statements - Prevention

Obtain special instructions before use

Do not handle until all safety precautions have been read and understood

Use personal protective equipment as required

Precautionary Statements - Response

IF exposed or concerned: Get medical advice/attention

Precautionary Statements - Storage

Store locked up

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant

Hazards not otherwise classified (HNOC)**Other information**

- May be harmful if swallowed
 - May be harmful in contact with skin
- No information available

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical name	CAS No.	Weight-%	Trade Secret
Limestone	1317-65-3	30 - 60	*
Proprietary - Silyl Terminated Polyether	Undisclosed	10 - 30	*
Polypropylene glycol	25322-69-4	10 - 30	*
Aminoethyl aminopropyl trimethoxy silane	1760-24-3	1 - 5	*
Dibutyltin Diacetyldiacetonate	22673-19-4	0.1 - 1	*

* The exact percentage (concentration) of composition has been withheld as a trade secret.

4. FIRST AID MEASURES**Description of first aid measures**

General advice	If symptoms persist, call a physician. Do not get in eyes, on skin, or on clothing.
Eye contact	Immediately flush with plenty of water. After initial flushing, remove any contact lenses and continue flushing for at least 15 minutes. Keep eye wide open while rinsing. If symptoms persist, call a physician.
Skin Contact	Wipe off material with a dry cloth. Wash with soap and water. If skin irritation persists, call a physician.
Inhalation	Remove to fresh air. If symptoms persist, call a physician.
Ingestion	Do NOT induce vomiting. Rinse mouth. Never give anything by mouth to an unconscious person. Call a physician.
Self-protection of the first aider	Use personal protective equipment as required.

Most important symptoms and effects, both acute and delayed

Symptoms May cause irritation. May be harmful if swallowed.

Indication of any immediate medical attention and special treatment needed

Note to physicians Treat symptomatically.

5. FIRE-FIGHTING MEASURES**Suitable Extinguishing Media**

Use. Dry chemical. Carbon dioxide (CO₂). Water spray (fog). Alcohol resistant foam.

Unsuitable Extinguishing Media Caution: Use of water spray when fighting fire may be inefficient.

Specific hazards arising from the chemical

No information available.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions Avoid contact with skin, eyes or clothing. Use personal protective equipment as required.

Environmental precautions

Environmental precautions Do not flush into surface water or sanitary sewer system. Prevent product from entering drains. See Section 12 for additional ecological information.

Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Dam up. Soak up with inert absorbent material. Pick up and transfer to properly labeled containers. Clean contaminated surface thoroughly.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Avoid contact with skin, eyes or clothing. Use personal protective equipment as required. Wash contaminated clothing before reuse.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep out of the reach of children. Keep containers tightly closed in a cool, well-ventilated place. Keep in properly labeled containers.

Incompatible materials Incompatible with oxidizing agents. Acids.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines

Chemical name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Limestone 1317-65-3		TWA: 15 mg/m ³ total dust TWA: 5 mg/m ³ respirable fraction (vacated) TWA: 15 mg/m ³ total dust (vacated) TWA: 5 mg/m ³ respirable fraction	TWA: 10 mg/m ³ total dust TWA: 5 mg/m ³ respirable dust
Dibutyltin Diacetyldiacetonate 22673-19-4	STEL: 0.2 mg/m ³ Sn TWA: 0.1 mg/m ³ Sn S*	TWA: 0.1 mg/m ³ Sn (vacated) TWA: 0.1 mg/m ³ Sn (vacated) S*	IDLH: 25 mg/m ³ Sn TWA: 0.1 mg/m ³ except Cyhexatin Sn

NIOSH IDLH *Immediately Dangerous to Life or Health*

Other information

Vacated limits revoked by the Court of Appeals decision in AFL-CIO v. OSHA, 965 F.2d 962 (11th Cir., 1992).

Appropriate engineering controls

Engineering Controls None under normal use conditions.

Individual protection measures, such as personal protective equipment

Eye/face protection Wear safety glasses with side shields (or goggles).

Skin and body protection Gloves.

Respiratory protection If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

General Hygiene Considerations Avoid contact with skin, eyes or clothing. Wash contaminated clothing before reuse. When using do not eat, drink or smoke. Regular cleaning of equipment, work area and clothing is recommended.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical state	Liquid	Odor	Mild
Appearance	viscous	Odor threshold	No information available
Color	light brown		
Property	Values	Remarks • Method	
pH	Not Applicable	Not Applicable	
Melting point / freezing point °F	No information available	Not Applicable	
Boiling point / boiling range	No information available		
Flash point	> 93 °C / > 200 °F		
Evaporation rate	No information available		
Flammability (solid, gas)	No information available		
Flammability Limit in Air			
Upper flammability limit:	No information available		
Lower flammability limit:	No information available		
Vapor pressure	No information available		
Vapor density	No information available		
Specific gravity	1.4-1.55		
Water solubility			
Solubility in other solvents	No information available		
Partition coefficient	No information available		
Autoignition temperature	No information available		
Decomposition temperature	No information available		
Kinematic viscosity	No information available		
Dynamic viscosity	No information available		
Explosive properties	Not Applicable		
Oxidizing properties	Not Applicable		

10. STABILITY AND REACTIVITY

Reactivity

No data available

Chemical stability

Stable under recommended storage conditions.

Possibility of hazardous reactions

None under normal processing.

Conditions to avoid

None known based on information supplied.

Incompatible materials

Incompatible with oxidizing agents. Acids.

Hazardous decomposition products

Carbon oxides. Unidentified organic compounds.

11. TOXICOLOGICAL INFORMATION**Information on likely routes of exposure**

Product Information	May cause irritation
Inhalation	Avoid breathing vapors or mists.
Eye contact	Avoid contact with eyes.
Skin Contact	Avoid contact with skin.
Ingestion	Do not taste or swallow.

Component Information

Chemical name	LD50/Oral	LD50/Dermal	Inhalation LC50
Polypropylene glycol 25322-69-4	> 2 g/kg (Rat)		
Aminoethyl aminopropyl trimethoxy silane 1760-24-3	= 7460 µL/kg (Rat)		

Symptoms related to the physical, chemical and toxicological characteristics

Symptoms May cause irritation. May be harmful if swallowed.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization	No information available.
Germ cell mutagenicity	No information available.
Carcinogenicity	This product does not contain any carcinogens or potential carcinogens as listed by OSHA, IARC or NTP.
Reproductive toxicity	May damage fertility or the unborn child.
STOT - single exposure	No information available.
STOT - repeated exposure	No information available.
Target organ effects	Eyes, lungs, Respiratory system, Skin.
Aspiration hazard	No information available.

Numerical measures of toxicity - Product Information

Unknown acute toxicity	No information available
The following values are calculated based on chapter 3.1 of the GHS document .	
ATEmix (oral)	4967 mg/kg
ATEmix (dermal)	3534 mg/kg mg/l

12. ECOLOGICAL INFORMATION**Ecotoxicity**

Persistence and degradability

No information available.

Bioaccumulation

No information available.

Other adverse effects

No information available

13. DISPOSAL CONSIDERATIONS**Waste treatment methods****Disposal of wastes**

Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated packaging

Do not reuse container.

14. TRANSPORT INFORMATION**DOT**

Not Regulated for all modes of transportation.

15. REGULATORY INFORMATION**International Inventories****TSCA** Complies**DSL/NDSL** Complies**Legend:***TSCA - United States Toxic Substances Control Act Section 8(b) Inventory**DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List***US Federal Regulations****SARA 313**

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

SARA 311/312 Hazard Categories

Acute health hazard	Yes
Chronic Health Hazard	No
Fire hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

US State Regulations

California Proposition 65

U.S. State Right-to-Know Regulations

Chemical name	New Jersey	Massachusetts	Pennsylvania
Limestone 1317-65-3	X	X	X
Quartz 14808-60-7	X	X	X
Bis (2-ethylhexyl) adipate 103-23-1	X	X	X

16. OTHER INFORMATION

NFPA	Health hazards 1	Flammability 0	Instability 0	Physical and chemical properties -
HMIS	Health hazards 1	Flammability 0	Physical hazards 0	Personal protection X

Prepared By Regulatory Department
 Issuing Date 17-Oct-2014
 Revision date 29-Aug-2018
 Revision Note
 SDS sections updated 2 4 15

Disclaimer

The information contained on the Safety Data Sheet has been compiled from data considered accurate. This data is believed to be reliable, but it must be pointed out that values for certain properties are known to vary from source to source. PROSOCO, Inc. expressly disclaims any warranty express or implied as well as any liability for any injury or loss arising from the use of this information or the materials described. This data is not to be construed as absolutely complete since additional data may be desirable when particular conditions or circumstances exist. It is the responsibility of the user to determine the best precautions necessary for the safe handling and use of this product for his unique application. This data relates only to the specific material designated and is not to be used in combination with any other material. Many federal and state regulations pertain directly or indirectly to the product's end use and disposal of containers and unused material. It is the purchaser's responsibility to familiarize himself with all applicable regulations.

End of Safety Data Sheet