

**1. Identification**

Product name : SikaQuick® Winter Boost

Supplier : Sika Corporation
201 Polito Avenue
Lyndhurst, NJ 07071
USA
www.sikausa.com

Telephone : (201) 933-8800

Telefax : (201) 804-1076

E-mail address : ehs@sika-corp.com

Emergency telephone : CHEMTREC: 800-424-9300
INTERNATIONAL: 703-527-3887

Recommended use of the chemical and restrictions on use : For further information, refer to product data sheet.

2. Hazards identification**GHS Classification**

Skin corrosion, Category 1B H314: Causes severe skin burns and eye damage.
Serious eye damage, Category 1 H318: Causes serious eye damage.
Carcinogenicity, Category 1A (Inhalation) H350i: May cause cancer by inhalation.

GHS label elements

Hazard pictograms :



Signal Word : Danger

Hazard Statements : H314 Causes severe skin burns and eye damage.
H350i May cause cancer by inhalation.

Precautionary Statements : **Prevention:**
P201 Obtain special instructions before use.
P202 Do not handle until all safety precautions have been read and understood.
P260 Do not breathe dusts or mists.
P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.
P281 Use personal protective equipment as required.
Response:
P301 + P330 + P331 IF SWALLOWED: Rinse mouth. Do NOT



induce vomiting.

P303 + P361 + P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.

P304 + P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.

P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P308 + P313 IF exposed or concerned: Get medical advice/attention.

P310 Immediately call a POISON CENTER/doctor.

P363 Wash contaminated clothing before reuse.

Storage:

P405 Store locked up.

Disposal:

P501 Dispose of contents/ container to an approved waste disposal plant.

See Section 11 for more detailed information on health effects and symptoms.

There are no hazards not otherwise classified that have been identified during the classification process.

There are no ingredients with unknown acute toxicity used in a mixture at a concentration $\geq 1\%$.

3. Composition/information on ingredients

Hazardous ingredients

Chemical name	CAS-No.	Concentration (%)
sodium-aluminate	1302-42-7	$\geq 20 - < 25 \%$
Trade Secret	Proprietary	$\geq 10 - < 20 \%$
Quartz (SiO ₂)	14808-60-7	$\geq 0.1 - < 1 \%$

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment and hence require reporting in this section.

4. First aid measures

- | | |
|-------------------------|--|
| If inhaled | : Move to fresh air.
Consult a physician after significant exposure. |
| In case of skin contact | : Take off contaminated clothing and shoes immediately.
Wash off with soap and plenty of water.
Immediate medical treatment is necessary as untreated wounds from corrosion of the skin heal slowly and with difficulty. |
| In case of eye contact | : Small amounts splashed into eyes can cause irreversible tissue damage and blindness.
In the case of contact with eyes, rinse immediately with plenty of water and seek medical advice. |



	Continue rinsing eyes during transport to hospital. Remove contact lenses. Keep eye wide open while rinsing.
If swallowed	: Clean mouth with water and drink afterwards plenty of water. Do not induce vomiting without medical advice. Do not give milk or alcoholic beverages. Never give anything by mouth to an unconscious person. Take victim immediately to hospital.
Most important symptoms and effects, both acute and delayed	: Health injuries may be delayed. corrosive effects carcinogenic effects Prolonged exposure can cause silicosis. Dermatitis See Section 11 for more detailed information on health effects and symptoms. Causes serious eye damage. May cause cancer by inhalation. Causes severe burns.
Protection of first-aiders	: Move out of dangerous area. Consult a physician. Show this material safety data sheet to the doctor in attendance.
Notes to physician	: Treat symptomatically.

5. Fire-fighting measures

Suitable extinguishing media	: Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Specific extinguishing methods	: Collect contaminated fire extinguishing water separately. This must not be discharged into drains. Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations.
Special protective equipment for fire-fighters	: In the event of fire, wear self-contained breathing apparatus.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	: Use personal protective equipment. Avoid breathing dust. Deny access to unprotected persons.
Environmental precautions	: Do not flush into surface water or sanitary sewer system. If the product contaminates rivers and lakes or drains inform respective authorities. Local authorities should be advised if significant spillages



cannot be contained.

Methods and materials for containment and cleaning up : Pick up and arrange disposal without creating dust.
Keep in suitable, closed containers for disposal.

7. Handling and storage

Advice on safe handling : Avoid exceeding the given occupational exposure limits (see section 8).
Do not get in eyes, on skin, or on clothing.
For personal protection see section 8.
Smoking, eating and drinking should be prohibited in the application area.
Follow standard hygiene measures when handling chemical products.

Conditions for safe storage : Prevent unauthorized access.
Store in original container.
Keep container tightly closed in a dry and well-ventilated place.
Observe label precautions.
Store in accordance with local regulations.

Materials to avoid : No data available

8. Exposure controls/personal protection

Component	CAS-No.	Basis **	Value	Exposure limit(s)* / Form of exposure
Limestone	1317-65-3	OSHA Z-1	TWA	15 mg/m3 total dust
		OSHA Z-1	TWA	5 mg/m3 respirable fraction
		OSHA P0	TWA	15 mg/m3 Total
		OSHA P0	TWA	5 mg/m3 Respirable fraction
		OSHA P0	TWA	15 mg/m3 Total dust
		OSHA P0	TWA	5 mg/m3 respirable dust fraction
Quartz (SiO ₂)	14808-60-7	OSHA Z-3	TWA	10 mg/m3 / %SiO ₂ +2 respirable
		OSHA Z-3	TWA	



				250 mppcf / %SiO ₂ +5 respirable
		OSHA P0	TWA	0.1 mg/m ³ Respirable fraction
		ACGIH	TWA	0.025 mg/m ³ Respirable fraction
		OSHA Z-1	TWA	0.05 mg/m ³ Respirable dust

*The above mentioned values are in accordance with the legislation in effect at the date of the release of this safety data sheet.

****Basis**

ACGIH. Threshold Limit Values (TLV)

OSHA P0. Table Z-1, Limit for Air Contaminant (1989 Vacated Values)

OSHA P1. Permissible Exposure Limits (PEL), Table Z-1, Limit for Air Contaminant

OSHA P2. Permissible Exposure Limits (PEL), Table Z-2

OSHA Z3. Table Z-3, Mineral Dust

Engineering measures : Use of adequate ventilation should be sufficient to control worker exposure to airborne contaminants. If the use of this product generates dust, fumes, gas, vapor or mist, use process enclosures, local exhaust ventilation or other engineering controls to keep worker exposure below any recommended or statutory limits.

Personal protective equipment

Respiratory protection : Use a properly fitted NIOSH approved air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary.

The filter class for the respirator must be suitable for the maximum expected contaminant concentration (gas/vapor/aerosol/particulates) that may arise when handling the product. If this concentration is exceeded, self-contained breathing apparatus must be used.

Hand protection

Remarks : Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Eye protection : Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary.

Skin and body protection : Choose body protection in relation to its type, to the concentration and amount of dangerous substances, and to the specific work-place.



Hygiene measures : Avoid contact with skin, eyes and clothing.
Wash hands before breaks and immediately after handling the product.
Remove contaminated clothing and protective equipment before entering eating areas.
Wash thoroughly after handling.
Avoid breathing dust.

9. Physical and chemical properties

Appearance	: powder
Color	: white
Odor	: odorless
Odor Threshold	: No data available
Flash point	: Note: Not applicable
Ignition temperature	: No data available
Decomposition temperature	: No data available
Lower explosion limit (Vol%)	: No data available
Upper explosion limit (Vol%)	: No data available
Flammability (solid, gas)	: No data available
Oxidizing properties	: No data available
pH	: Note: Not applicable
Melting point/range /	: No data available
Freezing point	
Boiling point/boiling range	: No data available
Vapor pressure	: No data available
Density	: 1.1 g/cm ³ at 74.7 °F (23.7 °C)
Water solubility	: Note: insoluble
Partition coefficient: n- octanol/water	: No data available
Viscosity, dynamic	: No data available
Viscosity, kinematic	: Note: Not applicable
Relative vapor density	: No data available
Evaporation rate	: No data available



Burning rate : No data available

Volatile organic compounds (VOC) content : Not applicable

10. Stability and reactivity

Reactivity : No dangerous reaction known under conditions of normal use.

Chemical stability : The product is chemically stable.

Possibility of hazardous reactions : Stable under recommended storage conditions.

Conditions to avoid : No data available

Incompatible materials : No data available

11. Toxicological information

Acute toxicity

Not classified based on available information.

Components:

Trade secret

Acute oral toxicity : LD50 Oral (Rat): 613 mg/kg

Skin corrosion/irritation

Causes severe burns.

Serious eye damage/eye irritation

Causes serious eye damage.

Respiratory or skin sensitization

Skin sensitization: Not classified based on available information. Respiratory sensitization: Not classified based on available information.

Germ cell mutagenicity

Not classified based on available information.

Reproductive toxicity

Not classified based on available information.

STOT-single exposure

Not classified based on available information.

STOT-repeated exposure

Prolonged exposure can cause silicosis.

Aspiration toxicity

Not classified based on available information.

**Carcinogenicity**

May cause cancer by inhalation.

IARC

Group 1: Carcinogenic to humans

NTP

Quartz (SiO₂) 14808-60-7
Known to be human carcinogen

Quartz (SiO₂) 14808-60-7

12. Ecological information

Other information

Do not empty into drains; dispose of this material and its container in a safe way.

13. Disposal considerations**Disposal methods**

Waste from residues : Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements.

Contaminated packaging : Empty containers should be taken to an approved waste handling site for recycling or disposal.

14. Transport information**DOT**

UN number 3262
Description of the goods Corrosive solid, basic, inorganic, n.o.s.
(Sodium aluminate)
Class 8
Packing group III
Labels 8
Emergency Response 154
Guidebook Number

IATA

UN number 3262
Description of the goods Corrosive solid, basic, inorganic, n.o.s.
(Sodium aluminate)
Class 8
Packing group III
Labels 8
Packing instruction (cargo aircraft) 864
Packing instruction (passenger aircraft) 860



Packing instruction (passenger aircraft) Y845

IMDG

UN number 3262
Description of the goods CORROSIVE SOLID, BASIC, INORGANIC, N.O.S.
(Sodium aluminate)
Class 8
Packing group III
Labels 8
EmS Number 1 F-A
EmS Number 2 S-B

Marine pollutant no

DOT: For Limited Quantity exceptions reference 49 CFR 173.154 (b)
IMDG: For Limited Quantity special provisions reference IMDG Code Chapter 3.4

Special precautions for user

No data available

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not applicable

15. Regulatory information

TSCA list : All chemical substances in this product are either listed on the TSCA Inventory or are in compliance with a TSCA Inventory exemption.

EPCRA - Emergency Planning and Community Right-to-Know**CERCLA Reportable Quantity**

This material does not contain any components with a CERCLA RQ.

SARA304 Reportable Quantity

This material does not contain any components with a section 304 EHS RQ.

SARA 311/312 Hazards : Skin corrosion or irritation
Serious eye damage or eye irritation
Carcinogenicity

SARA 302 : This material does not contain any components with a section 302 EHS TPQ.

SARA 313 : This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

Clean Air Act

**Ozone-Depletion Potential**

This product neither contains, nor was manufactured with a Class I or Class II ODS as defined by the U.S. Clean Air Act Section 602 (40 CFR 82, Subpt. A, App.A + B).

This product does not contain any hazardous air pollutants (HAP), as defined by the U.S. Clean Air Act Section 112 (40 CFR 61).

This product does not contain any chemicals listed under the U.S. Clean Air Act Section 112(r) for Accidental Release Prevention (40 CFR 68.130, Subpart F).

California Prop 65

WARNING: Cancer – www.P65Warnings.ca.gov

16. Other information**HMIS Classification**

Health	*	3
Flammability		0
Physical Hazard		0
Personal Protection		X

Caution: HMIS® rating is based on a 0-4 rating scale, with 0 representing minimal hazards or risks, and 4 representing significant hazards or risks. Although HMIS® rating is not required on SDSs under 29 CFR 1910.1200, the preparer may choose to provide them. HMIS® rating is to be used with a fully implemented HMIS® program. HMIS® is a registered mark of the National Paint & Coatings Association (NPCA). Please note HMIS® attempts to convey full health warning information to all employees.

Notes to Reader

The information contained in this Safety Data Sheet applies only to the actual Sika Corporation ("Sika") product identified and described herein. This information is not intended to address, nor does it address the use or application of the identified Sika product in combination with any other material, product or process. All of the information set forth herein is based on technical data regarding the identified product that Sika believes to be reliable as of the date hereof. Prior to each use of any Sika product, the user must always read and follow the warnings and instructions on the product's current Product Data Sheet, product label and Safety Data Sheet for each Sika product, which are available at web site and/or telephone number listed in Section 1 of this SDS.

SIKA MAKES NO WARRANTIES EXPRESS OR IMPLIED AND ASSUMES NO LIABILITY ARISING FROM THIS INFORMATION OR ITS USE. SIKA SHALL NOT BE LIABLE UNDER ANY LEGAL THEORY FOR SPECIAL OR CONSEQUENTIAL DAMAGES AND SHALL NOT BE RESPONSIBLE FOR THE USE OF THIS PRODUCT IN A MANNER TO INFRINGE ON ANY PATENT OR ANY OTHER INTELLECTUAL PROPERTY RIGHTS HELD BY OTHERS.

All sales of Sika products are subject to its current terms and conditions of sale available at www.sikausa.com or 201-933-8800.

Revision Date 10/19/2018

Material number: 578241

