

MasterProtect 100CR PART A

Version 1.0 Revision Date: 09/15/2020 SDS Number: 000000261118 Date of last issue: -
Date of first issue: 09/15/2020

SECTION 1. IDENTIFICATION

Product name : MasterProtect 100CR PART A
Product code : 000000000051701541 000000000051701541

Manufacturer or supplier's details

Company name of supplier : Master Builders-Admixtures US,LLC
Address : 23700 CHAGRIN BLVD
Beachwood OH 44122
Emergency telephone : ChemTel: +1-813-248-0585 USA: +1-800-255-3924 Contract
Number MIS9240420

Recommended use of the chemical and restrictions on use

Recommended use : Product for construction chemicals
Restrictions on use : Reserved for industrial and professional use.

SECTION 2. HAZARDS IDENTIFICATION**GHS classification in accordance with 29 CFR 1910.1200**

Skin corrosion/irritation : 2
Serious eye damage/eye irritation : Category 2A
Skin sensitization : Category 1
Short-term (acute) aquatic hazard : 2
Long-term (chronic) aquatic hazard : 2

GHS label elements

Hazard pictograms : 

Signal Word : Warning

Hazard Statements : H319 Causes serious eye irritation.
H315 Causes skin irritation.
H317 May cause an allergic skin reaction.
H401 Toxic to aquatic life.
H411 Toxic to aquatic life with long lasting effects.

Precautionary Statements : **Prevention:**
P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.
P261 Avoid breathing dust/ fume/ gas/ mist/ vapours/ spray.
P273 Avoid release to the environment.
P272 Contaminated work clothing should not be allowed out of

MasterProtect 100CR PART A

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	09/15/2020	000000261118	Date of first issue: 09/15/2020

the workplace.
P264 Wash face, hands and any exposed skin thoroughly after handling.

Response:

P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P333 + P311 If skin irritation or rash occurs: Call a POISON CENTER or doctor/physician.

P303 + P352 IF ON SKIN (or hair): Wash with plenty of soap and water.

P332 + P313 If skin irritation occurs: Get medical advice/ attention.

P362 + P364 Take off contaminated clothing and wash it before reuse.

P391 Collect spillage.

P337 + P311 If eye irritation persists: Call a POISON CENTER or doctor/physician.

Disposal:

P501 Dispose of contents/container to appropriate hazardous waste collection point.

Other hazards

No data available.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical nature : No data available.

Components

Chemical name	CAS-No.	Concentration (% w/w)
Reaction product: bisphenol-A-(epichlorhydrin)-Epoxy resin (number average molecular weight <= 700)	25068-38-6	>= 50 - < 75
oxirane, mono[(C12-14-alkyloxy)methyl] derivs.	68609-97-2	>= 10 - < 15
Glass, oxide, chemicals	65997-17-3	>= 1 - < 5
Benzyl alcohol	100-51-6	>= 1 - < 3
Titanium dioxide	13463-67-7	>= 1 - < 3

SECTION 4. FIRST AID MEASURES

General advice : Move out of dangerous area.
Show this material safety data sheet to the doctor in attendance.
Do not leave the victim unattended.

If inhaled : If unconscious, place in recovery position and seek medical advice.

If symptoms persist, call a physician.

In case of skin contact : If skin irritation persists, call a physician.
If on skin, rinse well with water.

MasterProtect 100CR PART A

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	09/15/2020	000000261118	Date of first issue: 09/15/2020

In case of eye contact	:	If on clothes, remove clothes. Immediately flush eye(s) with plenty of water. Remove contact lenses. Protect unharmed eye. Keep eye wide open while rinsing. If eye irritation persists, consult a specialist.
If swallowed	:	Keep respiratory tract clear. Do not give milk or alcoholic beverages. Never give anything by mouth to an unconscious person. If symptoms persist, call a physician.
Most important symptoms and effects, both acute and delayed	:	Causes skin irritation. May cause an allergic skin reaction. Causes serious eye irritation.
Notes to physician	:	Treat symptomatically.

SECTION 5. FIRE-FIGHTING MEASURES

Suitable extinguishing media	:	Water spray Foam Dry powder Carbon dioxide (CO ₂)
Unsuitable extinguishing media	:	High volume water jet
Specific hazards during fire fighting	:	Do not allow run-off from fire fighting to enter drains or water courses.
Further information	:	Collect contaminated fire extinguishing water separately. This must not be discharged into drains. Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations.
Special protective equipment for fire-fighters	:	Wear self-contained breathing apparatus for firefighting if necessary.

SECTION 6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures	:	Use personal protective equipment.
Environmental precautions	:	Prevent product from entering drains. Prevent further leakage or spillage if safe to do so. If the product contaminates rivers and lakes or drains inform respective authorities.
Methods and materials for containment and cleaning up	:	Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Keep in suitable, closed containers for disposal.

SECTION 7. HANDLING AND STORAGE

Advice on protection against fire and explosion	:	Product is not explosive. Normal measures for preventive fire protection.
---	---	--

MasterProtect 100CR PART A

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	09/15/2020	000000261118	Date of first issue: 09/15/2020

- Advice on safe handling : Do not breathe vapors/dust.
Avoid exposure - obtain special instructions before use.
Avoid contact with skin and eyes.
For personal protection see section 8.
Smoking, eating and drinking should be prohibited in the application area.
Dispose of rinse water in accordance with local and national regulations.
Persons susceptible to skin sensitization problems or asthma, allergies, chronic or recurrent respiratory disease should not be employed in any process in which this mixture is being used.
- Conditions for safe storage : Keep container tightly closed in a dry and well-ventilated place.
Containers which are opened must be carefully resealed and kept upright to prevent leakage.
Electrical installations / working materials must comply with the technological safety standards.
- Further information on storage conditions : Keep only in the original container in a cool, dry, well-ventilated place away from ignition sources, heat or flame.
Protect from direct sunlight.
- Materials to avoid : Observe VCI storage rules.
- Recommended storage temperature : 41 °F / 5 °C
- Further information on storage stability : Minimum storage temperature:

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Ingredients with workplace control parameters

Components	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
Titanium dioxide	13463-67-7	TWA value	10 mg/m3	ACGIH TLV
		PEL (Total dust)	15 mg/m3	29 CFR 1910.1000 (Table Z-1)
		TWA value (Total dust)	10 mg/m3	29 CFR 1910.1000 (Table Z-1-A)
		TWA (total dust)	15 mg/m3	OSHA Z-1
		TWA (Total dust)	10 mg/m3	OSHA P0
		TWA	10 mg/m3 (Titanium dioxide)	ACGIH
Glass, oxide, chemicals	65997-17-3	TWA value (Inhalable fraction)	5 mg/m3	ACGIH TLV
		REL value (Fiber, total)	5 mg/m3	NIOSH
		REL value	5 mg/m3	NIOSH

MasterProtect 100CR PART A

Version 1.0 Revision Date: 09/15/2020 SDS Number: 000000261118 Date of last issue: -
 Date of first issue: 09/15/2020

		(fibers, total dust)		
		REL value (Fiber)	3 fibers/cm ³	NIOSH
		REL value (Fibrous dust)	3 fibers/cm ³	NIOSH
		TWA value (Fiber)	1 fibers/cm ³	ACGIHTLV
		TWA value (Fiber)	0.2 fibers/cm ³	ACGIHTLV
		TWA (fibers)	1 fibres per cubic centimeter	ACGIH
		TWA (Inhalable particulate matter)	5 mg/m ³	ACGIH
		TWA (fibers)	1 fibres per cubic centimeter	ACGIH
		TWA (fibers)	1 fibres per cubic centimeter	ACGIH

Engineering measures : No applicable information available.

Personal protective equipment

Respiratory protection : When workers are facing concentrations above the occupational exposure limits they must use appropriate certified respirators.

Hand protection

Remarks : The suitability for a specific workplace should be discussed with the producers of the protective gloves.

Eye protection : Eye wash bottle with pure water
Tightly fitting safety goggles
Wear face-shield and protective suit for abnormal processing problems.

Skin and body protection : Impervious clothing
Choose body protection according to the amount and concentration of the dangerous substance at the work place.

Protective measures : Do not inhale gases/vapours/aerosols.
Avoid contact with the skin, eyes and clothing.
Avoid exposure - obtain special instructions before use.
Handle in accordance with good building materials hygiene and safety practice.

Hygiene measures : Wearing of closed work clothing is recommended.
When using do not eat or drink.
When using do not smoke.
Wash hands before breaks and at the end of workday.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance : gel

Color : white

Odor : amine-like

MasterProtect 100CR PART A

Version 1.0 Revision Date: 09/15/2020 SDS Number: 000000261118 Date of last issue: -
Date of first issue: 09/15/2020

Odor Threshold : No data available

pH : slightly alkaline

Melting point : No applicable information available.

Boiling point : 500 °F / 260 °C

Flash point : 450.00 °F / 232.22 °C

Evaporation rate : No applicable information available.

Flammability (solid, gas) : not highly flammable
Method: derived from flash point

Upper explosion limit / Upper flammability limit : No applicable information available.

Lower explosion limit / Lower flammability limit : No applicable information available.

Vapor pressure : No applicable information available.

Relative vapor density : Heavier than air.

Relative density : No applicable information available.

Density : 1.07 g/cm³ (68 °F / 20 °C)

Solubility(ies)
Water solubility : No data available

Solubility in other solvents : No applicable information available.

Partition coefficient: n-octanol/water : No data available.

Autoignition temperature : No data available

Decomposition temperature : No decomposition if stored and handled as prescribed/indicated.

Viscosity
Viscosity, dynamic : No applicable information available.

Viscosity, kinematic : No applicable information available.

Explosive properties : Not explosive
Not explosive

Oxidizing properties : Based on its structural properties the product is not classified as oxidizing.

MasterProtect 100CR PART A

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	09/15/2020	000000261118	Date of first issue: 09/15/2020

Sublimation point : No applicable information available.

Molecular weight : No data available

SECTION 10. STABILITY AND REACTIVITY

Reactivity : No decomposition if stored and applied as directed.

Chemical stability : No decomposition if stored and applied as directed.

Possibility of hazardous reactions : No decomposition if stored and applied as directed.

Conditions to avoid : See SDS section 7 - Handling and storage.

Incompatible materials : Strong acids
Strong bases
Strong oxidizing agents
Strong reducing agents

Hazardous decomposition products : irritant gases/vapours
carbon oxides

SECTION 11. TOXICOLOGICAL INFORMATION**Acute toxicity**

Not classified based on available information.

Product:

Acute oral toxicity : Remarks: No applicable information available.

Acute inhalation toxicity : Remarks: No applicable information available.

Acute dermal toxicity : Remarks: No applicable information available.

Skin corrosion/irritation

Causes skin irritation.

Product:

Remarks : May cause skin irritation and/or dermatitis.

Serious eye damage/eye irritation

Causes serious eye irritation.

Product:

Remarks : May cause irreversible eye damage.

Respiratory or skin sensitization**Skin sensitization**

May cause an allergic skin reaction.

Respiratory sensitization

Not classified based on available information.

Product:

Remarks : Causes sensitization.

MasterProtect 100CR PART A

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	09/15/2020	000000261118	Date of first issue: 09/15/2020

Germ cell mutagenicity

Not classified based on available information.

Carcinogenicity

Not classified based on available information.

Reproductive toxicity

Not classified based on available information.

STOT-single exposure

Not classified based on available information.

STOT-repeated exposure

Not classified based on available information.

Aspiration toxicity

Not classified based on available information.

Further information**Product:**

Remarks : No data available

SECTION 12. ECOLOGICAL INFORMATION**Ecotoxicity****Product:****Ecotoxicology Assessment**

Chronic aquatic toxicity : Toxic to aquatic life with long lasting effects.

Persistence and degradability**Product:**

Biodegradability : Remarks: Taking into consideration the properties of several ingredients, the product is estimated not to be readily biodegradable according to OECD classification.

Stability in water : Remarks: The product is slightly soluble in water. It can be eliminated from water by abiotic processes.

Bioaccumulative potential**Product:**

Bioaccumulation : Remarks: Because of the product's consistency and low water solubility, bioavailability is improbable.

Components:**oxirane, mono[(C12-14-alkyloxy)methyl] derivs.:**Partition coefficient: n- : log Pow: 7.25 (77 °F / 25 °C)
octanol/water : Method: other (calculated)
GLP: no

MasterProtect 100CR PART A

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	09/15/2020	000000261118	Date of first issue: 09/15/2020

Glass, oxide, chemicals:

Partition coefficient: n-octanol/water : Remarks: The value has not been determined because the substance is inorganic.

Titanium dioxide:

Partition coefficient: n-octanol/water : Remarks: not applicable

Mobility in soil**Product:**

Distribution among environmental compartments : Remarks: The substance will not evaporate into the atmosphere from the water surface.
Following exposure to soil, adsorption to solid soil particles is probable, therefore contamination of groundwater is not expected.
Following exposure to soil, adsorption to solid soil particles is unlikely, therefore contamination of groundwater is expected.

Other adverse effects**Product:**

Additional ecological information : An environmental hazard cannot be excluded in the event of unprofessional handling or disposal.
Toxic to aquatic life.
Toxic to aquatic life with long lasting effects.

SECTION 13. DISPOSAL CONSIDERATIONS**Disposal methods**

Waste from residues : Do not contaminate ponds, waterways or ditches with chemical or used container.
Dispose of in accordance with national, state and local regulations.
Do not discharge into drains/surface waters/groundwater.

Contaminated packaging : Contaminated packaging should be emptied as far as possible and disposed of in the same manner as the substance/product.

SECTION 14. TRANSPORT INFORMATION**International Regulations****IATA-DGR**

Not regulated as a dangerous good

IMDG-Code

Not regulated as a dangerous good

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not applicable for product as supplied.

MasterProtect 100CR PART A

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	09/15/2020	000000261118	Date of first issue: 09/15/2020

Domestic regulation**49 CFR**

Not regulated as a dangerous good

SECTION 15. REGULATORY INFORMATION**US State Regulations****Pennsylvania Right To Know**

Titanium dioxide	13463-67-7
Benzyl alcohol	100-51-6
carbon black	1333-86-4
Glass, oxide, chemicals listed	65997-17-3

New Jersey Right To Know

Titanium dioxide	13463-67-7
carbon black	1333-86-4
Glass, oxide, chemicals listed	65997-17-3

California Prop. 65

WARNING: This product can expose you to chemicals including Glass, oxide, chemicals, which is/are known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.


The ingredients of this product are reported in the following inventories:

TSCA : On the inventory, or in compliance with the inventory

SECTION 16. OTHER INFORMATION**Further information**

MasterProtect 100CR PART A

Version 1.0 Revision Date: 09/15/2020 SDS Number: 000000261118 Date of last issue: -
 Date of first issue: 09/15/2020

NFPA 704:**HMIS® IV:**

HEALTH		
FLAMMABILITY		
PHYSICAL HAZARD		

HMIS® ratings are based on a 0-4 rating scale, with 0 representing minimal hazards or risks, and 4 representing significant hazards or risks. The "*" represents a chronic hazard, while the "/" represents the absence of a chronic hazard.

Full text of other abbreviations

29 CFR 1910.1000 (Table Z-1-A)	: OSHA - Table Z-1-A (29 CFR 1910.1000)
29 CFR 1910.1000 (Table Z-1)	: OSHA - Table Z-1 (Limits for Air Contaminants) 29 CFR 1910.1000
ACGIH	: USA. ACGIH Threshold Limit Values (TLV)
ACGIHTLV	: American Conference of Governmental Industrial Hygienists - threshold limit values (US)
NIOSH	: NIOSH Pocket Guide to Chemical Hazards (US)
OSHA P0	: USA. OSHA - TABLE Z-1 Limits for Air Contaminants - 1910.1000
OSHA Z-1	: USA. Occupational Exposure Limits (OSHA) - Table Z-1 Limits for Air Contaminants
29 CFR 1910.1000 (Table Z-1-A) / TWA value	: Time Weighted Average (TWA):
29 CFR 1910.1000 (Table Z-1) / PEL	: Permissible exposure limit
ACGIH / TWA	: 8-hour, time-weighted average
ACGIHTLV / TWA value	: Time Weighted Average (TWA):
NIOSH / REL value	: Recommended exposure limit (REL):
OSHA P0 / TWA	: 8-hour time weighted average
OSHA Z-1 / TWA	: 8-hour time weighted average

AICS - Australian Inventory of Chemical Substances; ASTM - American Society for the Testing of Materials; bw - Body weight; CERCLA - Comprehensive Environmental Response, Compensation, and Liability Act; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DOT - Department of Transportation; DSL - Domestic Substances List (Canada); ECx - Concentration associated with x% response; EHS - Extremely Hazardous Substance; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; ERG - Emergency Response Guide; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; HMIS - Hazardous Materials Identification System; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dan-

MasterProtect 100CR PART A

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	09/15/2020	000000261118	Date of first issue: 09/15/2020

gerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisation for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; MSHA - Mine Safety and Health Administration; n.o.s. - Not Otherwise Specified; NFPA - National Fire Protection Association; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NTP - National Toxicology Program; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; RCRA - Resource Conservation and Recovery Act; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; RQ - Reportable Quantity; SADT - Self-Accelerating Decomposition Temperature; SARA - Superfund Amendments and Reauthorization Act; SDS - Safety Data Sheet; TCSI - Taiwan Chemical Substance Inventory; TSCA - Toxic Substances Control Act (United States); UN - United Nations; UNRTDG - United Nations Recommendations on the Transport of Dangerous Goods; vPvB - Very Persistent and Very Bioaccumulative

Revision Date : 09/15/2020

We support worldwide Responsible Care® initiatives. We value the health and safety of our employees, customers, suppliers and neighbors, and the protection of the environment. Our commitment to Responsible Care is integral to conducting our business and operating our facilities in a safe and environmentally responsible fashion, supporting our customers and suppliers in ensuring the safe and environmentally sound handling of our products, and minimizing the impact of our operations on society and the environment during production, storage, transport, use and disposal of our products.

IMPORTANT: WHILE THE DESCRIPTIONS, DESIGNS, DATA AND INFORMATION CONTAINED HEREIN ARE PRESENTED IN GOOD FAITH AND BELIEVED TO BE ACCURATE , IT IS PROVIDED FOR YOUR GUIDANCE ONLY. BECAUSE MANY FACTORS MAY AFFECT PROCESSING OR APPLICATION/USE, WE RECOMMEND THAT YOU MAKE TESTS TO DETERMINE THE SUITABILITY OF A PRODUCT FOR YOUR PARTICULAR PURPOSE PRIOR TO USE. NO WARRANTIES OF ANY KIND, EITHER EXPRESSED OR IMPLIED, INCLUDING WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE, ARE MADE REGARDING PRODUCTS DESCRIBED OR DESIGNS, DATA OR INFORMATION SET FORTH, OR THAT THE PRODUCTS, DESIGNS, DATA OR INFORMATION MAY BE USED WITHOUT INFRINGING THE INTELLECTUAL PROPERTY RIGHTS OF OTHERS. IN NO CASE SHALL THE DESCRIPTIONS, INFORMATION, DATA OR DESIGNS PROVIDED BE CONSIDERED A PART OF OUR TERMS AND CONDITIONS OF SALE. FURTHER, YOU EXPRESSLY UNDERSTAND AND AGREE THAT THE DESCRIPTIONS, DESIGNS, DATA, AND INFORMATION FURNISHED BY OUR COMPANY HEREUNDER ARE GIVEN GRATIS AND WE ASSUME NO OBLIGATION OR LIABILITY FOR THE DESCRIPTION, DESIGNS, DATA AND INFORMATION GIVEN OR RESULTS OBTAINED, ALL SUCH BEING GIVEN AND ACCEPTED AT YOUR RISK.

US / EN

MasterProtect 100CR PART A

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	09/15/2020	000000261118	Date of first issue: 09/15/2020
