

UPG Sealed Lead-Acid Battery

STAY POWERED®

Absorbant Glass Mat (AGM) technology for superior performance. Valve regulated, spill proof construction allows safe operation in any position. Approved for transport by air. D.O.T., I.A.T.A., F.A.A. and C.A.B. certified. U.L. recognized under file number MH 20567.

UPG No. 40760

UB1272

Maintenance-Free

Specification


Nominal Voltage	12 volts (6 cells)		
Nominal Capacity			
20-hr. (0.36A)	7.20 Ah		
10-hr. (0.68A)	6.80 Ah		
5-hr. (1.26A)	6.30 Ah		
1-hr. (4.90A)	4.90 Ah		
Approximate Weight	5 lbs (2.25 kgs)		
Internal Resistance (Approx.)	24mΩ		
Shelf Life (% of normal capacity at 68° F (20° C))			
	3 Months	6 Months	12 Months
	91%	83%	64%
Temperature Dependency of Capacity (20 hour rate)			
	104° F (40° C)	77° F (25° C)	32° F (0° C)
	102%	100%	85%
			5° F (-15° C)
			65%
AGM Operational Temperature			
Charge	32° F to 104° F (0° C to 40° C)		
Discharge	5° F to 113° F (-15° C to 45° C)		
AGM Storage Temperature	5° F to 104° F (-15° C to 40° C)		



Due to continuous improvements to our products, product may vary slightly from depiction.

Charge Method (Constant Voltage)		
Cycle Use (Repeating Use)		
Initial Current	2.16 A or smaller	
Control Voltage	14.6 - 14.8 V	
Float Use		
Control Voltage	13.6 - 13.8 V	


Physical Dimensions: in (mm)



L: 5.94 in (151 mm)
W: 2.58 in (65.5 mm)
H: 3.78 in (96.0 mm)
TH: 4.06 in (103 mm)

Tolerances are +/- 0.04 in. (+/- 1mm) and +/- 0.08 in. (+/- 2mm) for height dimensions. All data subject to change without notice.


Terminals




F Series (Faston Tabs)

Dimension Type	L	W	w	H	T
F1	6.50	4.75	6.00	5.00	0.80


Discharge Time vs. Discharge Current




Discharge Characteristics




Shelf Life & Storage




Cycle Life vs Depth of Discharge



Open Circuit Voltage vs Residual Capacity



Effect of Temperature on Capacity



Charge Current & Final Discharge Voltage

Application	Charge Voltage(V/Cell)			Max.Charge Current	Final Discharge Voltage V/Cell	Discharge Current(A)	Final Discharge Voltage V/Cell	Discharge Current(A)	Final Discharge Voltage V/Cell	Discharge Current(A)
	Temperature	Set Point	Allowable Range							
Cycle Use	25°C(77°F)	2.45	2.40~2.50	0.30C	1.75	0.2C>(A)	1.70	0.2C<(A)<0.5C	1.60	0.5C<(A)<1.0C
Standby	25°C(77°F)	2.30	2.27~2.30		1.30	>1.0C				