ADJUSTABLE ALUMINUM GANTRY CRANE - AHA-15-15-10-PNU *** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE *** ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON 180" - 4 3/16" 156 1/4" -8'' 162 7/8" 106 1/4" MIN 98 1/4" MIN 136 1/4" MAX 128 1/4" MAX 164 1/8" 3D VIEW SHOWN FOR REFERENCE ONLY **DIMENSION TOLERANCE ± 1/4"** I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS STANDARD FEATURES SPECIAL FEATURES REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION MODEL NUMBER IS AHA-15-15-10-PNU NONE Ρ CAPACITY IS 1,500 LBS. Р COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE BASE WIDTH IS 53 3/4" AND LOCAL REGULATIONS AND STANDARDS R MAX OVERALL HEIGHT IS 136 1/4" UNITS REQUIRING APPROVAL DRAWINGS OR 0 I-BEAM HEIGHT IS 8" MODIFIED ARE NON-RETURNABLE V I-BEAM FLANGE WIDTH IS 4 3/16" " [] As marked [] As drawn OVERALL I-BEAM LENGTH IS 180" Date: Signed: USABLE I-BEAM LENGTH IS 156 1/4" ADJUSTABLE UNDER I-BEAM HEIGHT Printed Name: 98 1/4" MIN LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING 128 1/4" MAX DISTRIBUTOR'S NAME: HEIGHT IS ADJUSTABLE IN 6" INCREMENTS W.O.# X CASTERS: (4) Ø12" X 3 1/2" WIDE VESTIL MANUFACTURING PNEUMATIC SWIVEL CASTERS WITH DRAWN BY: X FOUR LOCKING POSITIONS DATE: XX/XX/XX SALES: X CRANE MAY BE TAKEN APART AND BUNDLED WITH reference: X SCALE: 1:38 FILE NAME: (2) INCLUDED STRAPS FOR EASY TRANSPORT

QUOTED LEAD TIME: Y

QUOTE #

Χ

28-007-295

ALUMINÚM CONSTRUCTION