
ADJUSTABLE ALUMINUM GANTRY CRANE - AHA-15-8-8-PNU

APPROX WEIGHT: 268 lbs.

DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE *** ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



STANDARD FEATURES

SPECIAL FEATURES **NONE**

MODEL NUMBER IS AHA-15-8-8-PNU CAPACITY IS 1,500 LBS. BASE WIDTH IS 53 3/4" MAX OVERALL HEIGHT IS 110 1/4" I-BEAM HEIGHT IS6" I-BEAM FLANGE WIDTH IS3 5/16" **OVERALL I-BEAM LENGTH IS 96"** USABLE I-BEAM LENGTH IS 72 1/4" ADJUSTABLE UNDER I-BEAM HEIGHT 74 1/4" HEIGHT IS ADJUSTABLE IN 6" INCREMENTS

CASTERS: (4) Ø12" X 3 1/2" WIDE

PNEUMATIC SWIVEL CASTERS WITH

FOUR LOCKING POSITIONS

CRANE MAY BE TAKEN APART AND BUNDLED WITH (2) INCLUDED STRAPS FOR EASY TRANSPORT

ALUMINUM CONSTRUCTION

DIMENSION TOLERANCE ± 1/4"			
APPROVA	REPRESENTED SAT REQUIREMENTS. I A CONFIRM PR COMPLIANCE WITH AND LOCAL REQ UNITS REQUIRIN MODIFIED	I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS. UNITS REQUIRING APPROVAL DRAWINGS OR MODIFIED ARE NON-RETURNABLE [] As drawn [] As marked	
L	Signed:		_Date:
	Printed Name:	PON RECEIPT OF SIGNED	APPROVAL DRAWING
DISTRIBUTOR'S NAME:			P.O.# X
VESTIL MANUFACTURING			W.O.# X
DRAWN BY: ND		DATE: 07/11/13	SALES: X
	RENCE: X TED LEAD TIME: X	SCALE: 1:28	FILE NAME: 28-007-285