

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0022285044](#)
Status: **Active**
Overview: [KK Interconnect Systems](#)
Description: KK 254 Breakaway Header, Vertical, 4 Circuits, 0.38µm Gold (Au) Selective Plating, Mating Pin Length 8.13mm, with Kinked PC Tails

Documents:

3D Model	Product Specification PS-10-07-001 (PDF)
3D Model (PDF)	Packaging Specification PK-40873-0041-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	PCB Headers
Series	42375
Application	Board-to-Board, Signal, Wire-to-Board
Overview	KK Interconnect Systems
Product Name	KK 254
Taxonomy	PCB Headers and Receptacles
UPC	800753792463

Physical

Breakaway	Yes
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Durability (mating cycles max)	100
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	0.276/g
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.43mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	2.54mm
Plating min - Mating	0.381µm
Plating min - Termination	2.540µm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	See Product Specification



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[42375](#) Series

Mates With

KK 254 Crimp Housing [2695](#) , [7880](#) . KK 254
Top-Entry PCB Receptacle [4455](#) . C-Grid
Shunt Terminal Housing [7859](#)

Termination Interface: Style Through Hole

Electrical

Current - Maximum per Contact 4.0A
Voltage - Maximum 500V

Solder Process Data

Duration at Max. Process Temperature (seconds) 005
Lead-freeProcess Capability WAVE
Max. Cycles at Max. Process Temperature 001
Process Temperature max. C 260

Material Info

Engineering Number 42375-0459

Reference - Drawing Numbers

Packaging Specification PK-40873-0041-001
Product Specification PS-10-07-001
Sales Drawing SD-42375-001-001, SD-42375-001-002

This document was generated on 10/11/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION