
ADJUSTABLE STEEL GANTRY CRANE - KNOCKDOWN - AHSN-8-20-12

APPROX WEIGHT: 1292.20 lbs.

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE ***
ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



STANDARD FEATURES

MODEL NUMBER IS AHSN-8-20-12 CAPACITY IS 8,000 LBS.

BASE WIDTH IS 77 1/2"

MAX OVERALL HEIGHT IS 157 9/16"

I-BEAM HEIGHT IS 125/16"

I-BEAM FLANGE WIDTH IS 6 1/2"

OVERALL I-BEAM LENGTH IS 239 3/4"

USABLE I-BEAM LENGTH IS 209 3/4"

HEIGHT IS ADJUSTABLE IN 6" INCREMENTS

CASTERS: (4) Ø8" X 3" WIDE PHENOLIC

SWIVEL CASTERS WITH FOUR

LOCKING POSITIONS

SPECIAL FEATURES NONE

		DIMENS	SION TO	LERANCE	E ± 1/4"	
	-><024	I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS. UNITS REQUIRING APPROVAL DRAWINGS OR MODIFIED ARE NON-RETURNABLE [] As drawn [] As marked				
	-	Signed:			_Date:	
		Printed Name:				
			ED APPROVAL DRAWII	٧G		
DISTRIBUTO	OR'S	NAME:			P.O.# X	
VESTIL MANUFAC			TURING		W.O.# X	
DRAWN BY: DLS			DATE: 06/30/2014		SALES: X	
reference: X				SCALE: 1:44	FILE NAME:	
, ,			QUOTE #		28-007-343	