
ADJUSTABLE STEEL GANTRY CRANE - AHS-4-20-14

APPROX WEIGHT: 10/1.38 lbs.

DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGIN

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE ***
ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



STANDARD FEATURES

MODEL NUMBER IS AHS-4-20-14
CAPACITY IS 4,000 LBS.
BASE WIDTH IS 89 1/2"
MAX OVERALL HEIGHT IS 181 3/16"
I-BEAM HEIGHT IS 12 3/16"
I-BEAM FLANGE WIDTH IS 4"
OVERALL I-BEAM LENGTH IS 239 3/4"
USABLE I-BEAM LENGTH IS 209 3/4"
ADJUSTABLE UNDER I-BEAM HEIGHT
169" MAX
103" MIN
HEIGHT IS ADJUSTABLE IN 6" INCREMENTS

CASTERS: (4) Ø8" X 3" WIDE PHENOLIC

LOCKING POSITIONS

SWIVEL CASTERS WITH FOUR

SPECIAL FEATURES

NONE

I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS. UNITS REQUIRING APPROVAL DRAWINGS OR MODIFIED ARE NON-RETURNABLE

	[] As drawn	[] As marked	
Signed:		Date:	

DISTRIBUTOR'S NAME:

VESTIL MANUFACTURING

DRAWN BY: ND

REFERENCE: X

QUOTED LEAD TIME: Y

P.O.# X

W.O.# X

NO.# X

SALES: X

SCALE: 1:52

P.O.# X

W.O.# X

W.O.#

Χ