
## **EHLTX APPROACH RAMP - ARX-3665-5.5**

APPROX WEIGHT: 239.70 lbs. DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

\*\*\*ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE\*\*\*



ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON

PROJECT SIGN OFF

**SALES** 

ENG.

FAB.

**POWER** 

## STANDARD FEATURES

MODEL NUMBER IS ARX-3665-5.5 OVERALL WIDTH IS 39 1/2" USABLE WIDTH IS 36" OVERALL LENGTH IS 64 13/16" OVERALL HEIGHT IS 5 1/2" MAX CAPACITY IS 4,000LBS RISE 5 1/2" SLOPE 4.6° APPROX. 8% GRADE DURABLE LIQUID PAINT BLUE FINISH

## SPECIAL FEATURES NONE

IT IS THE END-USER'S RESPONSIBILITY TO DETERMINE IF THE ABOVE RAMP SLOPE WILL FUNCTION WITH THEIR PALLET TRUCK TO LOAD & UNLOAD PRODUCT ONTO THE EHLTX

				DIMENSION	TOLERANCE ± 1	/4
5.5	A P P R O V	REPRE REQUIRE C COMPL AND	NDERSIGNED, AGRI SENTED SATISFIES D MENTS. I ALSO AC ONFIRM PRODUCT IANCE WITH ALL AP LOCAL REGULATION DIFIED UNITS A [ ] As drawn	ESIGN AND I KNOWLEDG AND INSTAL PPLICABLE FE DNS AND STA	DIMENSION E MY DUTY TO LATION EDERAL, STATE ANDARDS. RETURNABLE	
	Ă	Signed:			_Date:	
DE FINISH	L	Printed Nan	ne: <i>L START UPON RECEII</i>	PT OF SIGNED	APPROVAL DRAWII	NG
FOR INTERNAL USE ONLY	DISTR	IBUTOR'S NAME:			P.O.# X	

QUOTE #

9/5/2017

W.O.#

SCALE: 1:10 FILE NAME:

SALES: X

27-007-011

VESTIL MANUFACTURING

C.HARKER

REFERENCE: X

QUOTED LEAD TIME: X