
## ELECTRIC HYDRAULIC SCISSOR LIFT TABLE - EHLT-E-2448-2-41

\*\*\* ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE \*\*\* ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



MODEL NUMBER IS EHLT-E-2448-2-41 PLATFORM WIDTH IS 24 3/8"

PLATFORM LENGTH IS 48 3/8"

**OVERALL LENGTH IS 48 3/8"** 

PLATFORM RAISED HEIGHT IS 41"

PLATFORM LOWERED HEIGHT IS 8"

TABLE CAPACITY (EVENLY DISTRIBUTED)

LOAD IS 2.000 LBS

INTERNAL POWER UNIT

CONTROL IS HANDHELD, 2 BUTTON,

**NEMA 4 PENDANT WITH** 

MINIMUM 8' USABLE COIL CORD

SAFETY MAINTENANCE PROPS, DISPLACEMENT STYLE

CYLINDERS INSTALLED ROD DOWN

EMERGENCY SAFETY STOP HYDRAULIC FUSES IN ALL

**CYLINDER** 

UNITS HAVE 2' TEST LEAD AND PIG TAIL

BASE FRAME AND LEGS: DURABLE LIQUID PAINT BLUE FINISH

DECK: TOUGH BAKED IN POWDER COATED BLUE FINISH

## PLEASE CIRCLE SPECIFICATIONS:

POWER	AC	DC	DC (12V		R/OIL
MOTOR V	115	208	230	460	
DEDICATED CIRCUIT REQUIRED 60Hz					
motor phase — s		SINCL	<del>INGLE  </del>		ree
CONTROL		HANI	HAND -		<del>OT </del>

## SPECIAL FEATURES NONE

I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL STATE AND LOCAL REGULATIONS AND STANDARDS UNITS REQUIRING APPROVAL DRAWINGS OR

DIMENSION TOLERANCE ± 1/4"

MODIFIED ARE NON-RETURNABLE [ ] As drawn [ ] As marked

Signed: Date: Printed Name:

LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING

DISTRIBUTOR'S NAME: VESTIL MANUFACTURING

W.O.# X

DRAWN BY: DLS DATE: 08/01/2022 SALES: X

reference: X SCALE: 1:14 FILE NAME: Quoted lead time:  $_{
m Y}$ 

QUOTE # Х

01-007-525