
APPROX WEIGHT: 1.10 lbs. DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

LEVER ACTION (POLYPROPYLENE) - VLDP

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE *** ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



STANDARD FEATURES

SPECIAL FEATURES

NONE MODEL NUMBER IS VLDP OVERALL WIDTH IS 4 3/4" OVERALL LENGTH IS 7 15/16" OVERALL HEIGHT IS 49 11/16" DISPLACEMENT PER STROKE IS 10oz. FITS 2" BUNG CONSTRUCTION POLYPROPYLENE HANDLES VISCOUS LIQUIDS UP TO 12,000 cPs (EQUIVALENT TO SAE 90 OIL). NOT FOR USE ABOVE 125°F OR WITH HEATED DRUMS.

	DIVILIATION TOLLIVANCE 1 1/4
	I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS
	REPRESENTED SATISFIES DESIGN AND DIMENSION
Α	REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO
Р	CONFIRM PRODUCT AND INSTALLATION
P	COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE
R	AND LOCAL REGULATIONS AND STANDARDS.
_	ALL SPECIAL UNITS ARE NON-RETURNABLE
0	[] As drawn [] As marked
V	[] / to aratim

Date:

DIMENSION TOLEDANCE + 1/4"

LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING

Signed:

OF CICINED AND THE BIT WINTE				
DISTRIBUTOR'S NAME:	P.O.# X			
VESTIL MANUFA	W.O.# X			
drawn by: RS	DATE: 08/2	22/2012	SALES: X	
reference: X	S	SCALE: 1:12	FILE NAME:	
QUOTED LEAD TIME: X	QUOTE #		40-007-058	