

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0003092062](#)  
**Status:** **Active**  
**Overview:** Standard .093" Pin and Socket Connectors  
**Description:** 2.36mm Diameter Standard .093" Pin and Socket Plug Housing, 6 Circuits, Dual Row

**Documents:**

|  |   |
|--|---|
| <a href="#">Drawing (PDF)</a>                            | <a href="#">Product Specification PS-43660-9999-001 (PDF)</a> |
| <a href="#">3D Model</a>                                 | <a href="#">Packaging Specification PK-1261-001-001 (PDF)</a> |
| <a href="#">3D Model (PDF)</a>                           | <a href="#">RoHS Certificate of Compliance (PDF)</a>          |
| <a href="#">Product Specification PS-02-09-001 (PDF)</a> |   |



*Series image - Reference only*

**Agency Certification**

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

**General**

|                |   |
|----------------|---|
| Product Family | Crimp Housings  |
| Series         | <a href="#">1261</a>  |
| Application    | Power, Wire-to-Wire   |
| Comments       | 14.0A max. can be achieved when housing is used with 42477 or 42478 terminals |
| Overview       | <a href="#">Standard .093" Pin and Socket Connectors</a>                      |
| Product Name   | Standard .093"  |
| Taxonomy       | Connector Housings  |
| UPC            | 800753618879  |

**Physical**

|                               |                |
|-------------------------------|----------------|
| Circuits (maximum)            | 6              |
| Color - Resin                 | Natural        |
| Flammability                  | 94V-2          |
| Gender                        | Plug           |
| Glow-Wire Capable             | No             |
| Material - Resin              | Nylon          |
| Net Weight                    | 3.160/g        |
| Number of Rows                | 2              |
| Packaging Type                | Bag            |
| Panel Mount                   | No             |
| Pitch - Mating Interface      | 5.03mm         |
| Pitch - Termination Interface | 5.03mm         |
| Stackable                     | No             |
| Temperature Range - Operating | -40° to +105°C |

**Solder Process Data**

|                             |     |
|-----------------------------|-----|
| Lead-freeProcess Capability | N/A |
|-----------------------------|-----|

**Material Info**

|                    |         |
|--------------------|---------|
| Engineering Number | 1261-P1 |
|--------------------|---------|

**Reference - Drawing Numbers**

|                         |                                 |
|-------------------------|---------------------------------|
| Packaging Specification | PK-1261-001-001                 |
| Product Specification   | PS-02-09-001, PS-43660-9999-001 |
| Sales Drawing           | 12610000-SD-000                 |

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[1261 Series](#)

**Mates With**

[03091061](#) , [03091062](#) , [03091063](#) , [03091064](#) , [03096061](#)

**Use With**

[1189 Crimp Terminals](#), [1190 Crimp Terminals](#), [1380 Male Crimp Terminals](#), [1381 Female Crimp Terminals](#), [1433 Crimp Terminals](#), [1434 Male Crimp Terminals](#), [1973](#) , [2151](#) , [2273](#) , [2870](#) , [2871](#) , [4272](#) , [Link:4550](#), [6271](#)