

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0015249147](#)
Status: **Active**
Overview: Mini-Fit Family Power Connectors
Description: Mini-Fit BMI Header, Dual Row, Right-Angle, with Snap-in Plastic Peg PCB Lock, 14 Circuits, PA Polyamide Nylon 6/6, UL 94V-2, with Select Gold (Au) Plating

Documents:

| | |
|--|--|
| 3D Model | Product Specification PS-5556-002-001 (PDF) |
| 3D Model (PDF) | Application Specification 424040001-AS-000 (PDF) |
| Drawing (PDF) | Packaging Specification PK-42404-002-001 (PDF) |
| Product Specification 55560002-PS-CH-000 (PDF) | Test Summary TS-42404-001-001 (PDF) |
| Product Specification 55560002-PS-ES-000 (PDF) | Test Summary TS-5556-002-001 (PDF) |
| Product Specification 55560002-PS-SK-000 (PDF) | Symbol Footprint Data SYM-A42404-14XX-001 (PDF) |
| Product Specification PS-45750-001-001 (PDF) | RoHS Certificate of Compliance (PDF) |

Agency Certification

| | |
|-----|---------|
| CSA | LR19980 |
| UL | E29179 |

General

| | |
|----------------|---|
| Product Family | PCB Headers |
| Series | 42404 |
| Application | Board-to-Board, Power, Wire-to-Board |
| Comments | Current = 13A max. per circuit when header is mated to a receptacle loaded with 45750 Mini-Fit Plus HCS Crimp Terminal Crimped to 16 AWG wire. See Molex product specification PS-45750-001 for additional current de-rating information. |
| Overview | Mini-Fit Family Power Connectors |
| Product Name | Mini-Fit BMI |
| Taxonomy | PCB Headers and Receptacles |
| UPC | 822350294973 |

Physical

| | |
|--------------------------------|-------------|
| Breakaway | No |
| Circuits (Loaded) | 14 |
| Circuits (maximum) | 14 |
| Color - Resin | Natural |
| Durability (mating cycles max) | 30 |
| Flammability | 94V-2 |
| Glow-Wire Capable | No |
| Guide to Mating Part | Yes |
| Lock to Mating Part | Yes |
| Material - Metal | Brass |
| Material - Plating Mating | Gold |
| Material - Plating Termination | Tin |
| Material - Resin | Nylon |
| Net Weight | 5.510/g |
| Number of Rows | 2 |
| Orientation | Right Angle |
| PC Tail Length | 3.30mm |
| PCB Locator | Yes |
| PCB Retention | Yes |
| PCB Thickness - Recommended | 1.80mm |
| Packaging Type | Tray |
| Pitch - Mating Interface | 4.20mm |
| Plating min - Mating | 0.762µm |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[42404 Series](#)

Mates With

[15060140](#) Mini-Fit BMI Panel Mount Receptacle, [39012140](#) Mini-Fit Jr. Receptacle, [15247142](#) Mini-Fit BMI Vertical Receptacle Header

| | |
|--------------------------------|----------------|
| Plating min - Termination | 2.540µm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | Yes |
| Shrouded | Partial |
| Stackable | No |
| Surface Mount Compatible (SMC) | No |
| Temperature Range - Operating | -40° to +105°C |
| Termination Interface: Style | Through Hole |

Electrical

| | |
|-------------------------------|-------|
| Current - Maximum per Contact | 13.0A |
| Voltage - Maximum | 600V |

Solder Process Data

| | |
|--|------|
| Duration at Max. Process Temperature (seconds) | 005 |
| Lead-free Process Capability | WAVE |
| Max. Cycles at Max. Process Temperature | 001 |
| Process Temperature max. C | 240 |

Material Info

| | |
|--------------------|------------|
| Engineering Number | 42404-14A5 |
|--------------------|------------|

Reference - Drawing Numbers

| | |
|---------------------------|---|
| Application Specification | 424040001-AS-000 |
| Packaging Specification | PK-42404-002-001 |
| Product Specification | 55560002-PS-CH-000, 55560002-PS-ES-000, 55560002-PS-SK-000, PS-45750-001-001, PS-5556-002-001 |
| Sales Drawing | SDA-42404-XXXX-001 |
| Symbol/Footprint Data | SYM-A42404-14XX-001 |
| Test Summary | TS-42404-001-001, TS-5556-002-001 |

This document was generated on 10/19/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION