

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0022032141](#)
Status: **Active**
Overview: [KK Interconnect Systems](#)
Description: KK 254 Wire-to-Board Header, Single Row, Vertical, 14 Circuits, PA Polyamide Nylon, Tin (Sn) Plating

Documents:

| | |
|--------------------------------|---|
| 3D Model (PDF) | Product Specification PS-10-07-001 (PDF) |
| Drawing (PDF) | Packaging Specification PK-4030-001-001 (PDF) |
| 3D Model | RoHS Certificate of Compliance (PDF) |

Agency Certification

| | |
|-----|---------|
| CSA | LR19980 |
| UL | E29179 |


General

| | |
|----------------|---|
| Product Family | PCB Headers |
| Series | 4030 |
| Application | Board-to-Board, Signal, Wire-to-Board |
| Overview | KK Interconnect Systems |
| Product Name | KK 254 |
| Taxonomy | PCB Headers and Receptacles |
| UPC | 800753735576 |

Physical

| | |
|--------------------------------|---------------------------|
| Breakaway | No |
| Circuits (Loaded) | 14 |
| Circuits (maximum) | 14 |
| Color - Resin | Natural (White) |
| Durability (mating cycles max) | 25 |
| Flammability | 94V-0 |
| Glow-Wire Capable | No |
| Lock to Mating Part | None |
| Material - Metal | Brass |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Material - Resin | Nylon |
| Net Weight | 0.961/g |
| Number of Rows | 1 |
| Orientation | Vertical |
| PC Tail Length | 3.43mm |
| PCB Locator | No |
| PCB Retention | None |
| PCB Thickness - Recommended | 1.60mm |
| Packaging Type | Bag |
| Pitch - Mating Interface | 2.54mm |
| Pitch - Termination Interface | 2.54mm |
| Plating min - Mating | 5.080µm |
| Polarized to Mating Part | No |
| Polarized to PCB | No |
| Shrouded | No |
| Stackable | Yes |
| Surface Mount Compatible (SMC) | No |
| Temperature Range - Operating | See Product Specification |
| Termination Interface: Style | Through Hole |

Electrical



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[4030 Series](#)

Mates With

KK 254 Crimp Housing [2695](#) , [7880](#) . KK 254
Top-Entry PCB Receptacle [4455](#) . C-Grid
Shunt Terminal Housing [7859](#)

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 4.0A |
| Voltage - Maximum | 500V |

Solder Process Data

| | |
|--|------|
| Duration at Max. Process Temperature (seconds) | 005 |
| Lead-free Process Capability | WAVE |
| Max. Cycles at Max. Process Temperature | 001 |
| Process Temperature max. C | 235 |

Material Info

| | |
|--------------------|---------------|
| Engineering Number | A-4030-14A197 |
|--------------------|---------------|

Reference - Drawing Numbers

| | |
|-------------------------|------------------|
| Packaging Specification | PK-4030-001-001 |
| Product Specification | PS-10-07-001 |
| Sales Drawing | SD-4030-0001-001 |

This document was generated on 10/13/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION