

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0192150023](#)
Status: **Active**
Overview: [Splices](#)
Description: Step Down Butt Splice for 10-16 AWG Wire

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E32244

General

Product Family Splices
 Series [19215](#)
 Comments Step down: 10/12 to 14/16 AWG
 Crimp Quality Equipment Yes
 Overview [Splices](#)
 Product Name Butt - Step Down
 Taxonomy Splices
 UPC 800755062502

Physical

Barrel Type Closed
 Insulation None
 Material - Metal Copper
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 2.694/g
 Packaging Type Bag
 Temperature Range - Operating 149°C
 Wire Insulation Diameter N/A
 Wire Size AWG 10, 14, 16, 2
 Wire Size mm² N/A

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Engineering Number CB-346

Reference - Drawing Numbers

Product Specification PS-19902-011-001, PS-19902-013-001
 Sales Drawing SD-19215-004-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2022)4187-DC (10
 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[19215 Series](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

| Description | Product # |
|--|---------------------------|
| PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm ² - 0.5mm ² | 640030100 |
| Crimp Head for the AT-200 Pneumatic Hand Tool | 640070100 |
| ServiceGrade Hand Crimp Tool - Ratchet | 640160038 |

This document was generated on 10/14/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION