

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0022122114

Status:

Active

Overview:

KK Interconnect Systems

Description:

KK 254 Solid Header, Right-Angle, with Friction Lock, 11 Circuits, 0.51µm Gold (Au) Plating

Documents:

- 3D Model

Packaging Specification PK-7478-001-000 (PDF)
- Drawing (PDF)

Symbol Footprint Data SYM-22-05-3111-001 (PDF)
- 3D Model (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification PS-10-07-001 (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Headers

Series

7478

Application

Signal, Wire-to-Board

Overview

KK Interconnect Systems

Product Name

KK 254

Taxonomy

PCB Headers and Receptacles

UPC

800753625556

Physical

Breakaway

No

Circuits (Loaded)

11

Circuits (maximum)

11

Color - Resin

Natural (White)

Durability (mating cycles max)

50

Flammability

94V-0

Glow-Wire Capable

No

Lock to Mating Part

Yes

Material - Metal

Brass

Material - Plating Mating

Gold

Material - Resin

Nylon

Net Weight

1.443/g

Number of Rows

1

Orientation

Right Angle

PC Tail Length

3.58mm

PCB Locator

No

PCB Retention

None

PCB Thickness - Recommended

1.60mm

Packaging Type

Bag

Pitch - Mating Interface

2.54mm

Pitch - Termination Interface

2.54mm

Polarized to Mating Part

Yes

Polarized to PCB

Yes

Shrouded

Partial

Stackable

Yes

Temperature Range - Operating

See Product Specification

Termination Interface: Style

Through Hole

Electrical

Current - Maximum per Contact

4.0A

Voltage - Maximum

500V



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

7478 Series

Mates With

2695 , 6471 , 7880 , 4455 , 7720

Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235

Material Info

Engineering Number	A-7478-11A241
--------------------	---------------

Reference - Drawing Numbers

Packaging Specification	PK-7478-001-000
Product Specification	PS-10-07-001
Sales Drawing	SDA-7478-000
Symbol/Footprint Data	SYM-22-05-3111-001

This document was generated on 10/17/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION