

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0022182121

Status:

Active

Overview:

KK Interconnect Systems

Description:

KK 254 PC Board Connector, Top Entry, with Cat Ear Terminal, 0.38µm Gold (Au), 12 Circuits, with Hooks

Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

Packaging Specification PK-44646-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA		LR19980
UL		E29179
General		
Product Family		PCB Receptacles
Series		4455
Application		Board-to-Board, Signal
Comments		With Hooks
Overview		KK Interconnect Systems
Product Name		KK 254
Taxonomy		PCB Headers and Receptacles
UPC		800754204972

Physical		
Circuits (Loaded)		12
Circuits (maximum)		12
Color - Resin		Natural (White)
Flammability		94V-0
Glow-Wire Capable		No
Guide to Mating Part		No
Keying to Mating Part		None
Lock to Mating Part		No
Material - Plating Mating		Gold
Material - Plating Termination		Tin
Material - Resin		Nylon
Net Weight		1.256/g
Number of Rows		1
Orientation		Vertical
PC Tail Length		3.35mm
PCB Locator		No
PCB Retention		None
PCB Thickness - Recommended		1.60mm
Packaging Type		Tray
Pitch - Mating Interface		2.54mm
Pitch - Termination Interface		2.54mm
Plating min - Mating		0.381µm
Plating min - Termination		2.540µm
Polarized to PCB		No
Surface Mount Compatible (SMC)		No
Temperature Range - Operating		See Product Specification
Termination Interface: Style		Through Hole

Electrical		
Current - Maximum per Contact		2.5A
Grounding to PCB		No



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

4455 Series

Mates With

KK Header [4094](#) , [42376](#) , [42375](#) , [42377](#) , [171856](#) , [171857](#)
SL Insulation Displacement Connector [70475](#)

Voltage - Maximum	500V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235
Material Info	
Engineering Number	A-4455-CZ12A(208)
Reference - Drawing Numbers	
Packaging Specification	PK-44646-001-001
Sales Drawing	SDA-4455-001

This document was generated on 10/17/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION