

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0022284121](#)  
**Status:** **Active**  
**Overview:** [KK Interconnect Systems](#)  
**Description:** KK 254 Breakaway Header, Vertical, 12 Circuits, Tin (Sn) Plating, Mating Pin Length 8.13mm

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-10-07-001 (PDF)</a>
<a href="#">3D Model</a>	<a href="#">Packaging Specification PK-40873-0041-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**Agency Certification**


CSA	LR19980
UL	E29179

**General**

Product Family	PCB Headers
Series	<a href="#">42375</a>
Application	Board-to-Board, Signal, Wire-to-Board
Overview	<a href="#">KK Interconnect Systems</a>
Product Name	KK 254
Taxonomy	PCB Headers and Receptacles
UPC	800753831308

**Physical**

Breakaway	Yes
Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	0.816/g
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.05mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	2.54mm
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	See Product Specification



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2022)4187-DC (10  
June 2022)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[42375 Series](#)

**Mates With**

KK 254 Crimp Housing [2695](#) , [7880](#) . KK 254  
Top-Entry PCB Receptacle [4455](#) . C-Grid  
Shunt Terminal Housing [7859](#)

Termination Interface: Style Through Hole

**Electrical**

Current - Maximum per Contact 4.0A  
Voltage - Maximum 500V

**Solder Process Data**

Duration at Max. Process Temperature (seconds) 005  
Lead-free Process Capability WAVE  
Max. Cycles at Max. Process Temperature 001  
Process Temperature max. C 235

**Material Info**

Engineering Number 42375-0117

**Reference - Drawing Numbers**

Packaging Specification PK-40873-0041-001  
Product Specification PS-10-07-001  
Sales Drawing SD-42375-001-001, SD-42375-001-002

This document was generated on 10/12/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**