

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0449141801](#)
Status: **Active**
Overview: [Micro-Fit Connector System](#)
Description: Micro-Fit CPI Header, Compliant Pin Interface, Dual Row, Vertical, 18 Circuits, Tin (Sn) Plating, Glow-Wire Capable

Documents:

- | | |
|---|--|
| Drawing (PDF) | Test Summary TS-43045-001-001 (PDF) |
| 3D Model (PDF) | Test Summary TS-43045-002-001 (PDF) |
| 3D Model | Test Summary TS-46235-001-001 (PDF) |
| Product Specification 430450001-PS-KO-000 (PDF) | Datasheet (PDF) |
| Product Specification 430450001-PS-SP-000 (PDF) | Symbol Footprint Data SYM-44914-1801-001 (PDF) |
| Product Specification PS-43045-001 (PDF) | RoHS Certificate of Compliance (PDF) |
| Packaging Specification PK-70873-0314-001 (PDF) | |

Agency Certification

CSA	LR19980
UL	E29179

Application tooling part link

Application Tooling Part Link	62203-0455
-------------------------------	------------


General

Product Family	PCB Headers
Series	44914
Application	Power, Wire-to-Board
Comments	High Temperature, Square Pin; This Molex product is manufactured from material that has the following ratings, tested by independent agencies: a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12 and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options.

Overview	Micro-Fit Connector System
Product Name	Micro-Fit CPI
Taxonomy	PCB Headers and Receptacles
UPC	756054636817

Physical

Breakaway	No
Circuits (Loaded)	18
Circuits (maximum)	18
Color - Resin	Black
Durability (mating cycles max)	30
Flammability	94V-0
Glow-Wire Capable	Yes



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[44914](#) Series

Mates With

[430251800](#) Micro-Fit 3.0 Receptacle
Housing

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Removal Tool

Product #

[622030455](#)

Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	2.425/g
Number of Rows	2
Orientation	Vertical
PCB Locator	Yes
PCB Retention	Yes
Packaging Type	Tray
Pitch - Mating Interface	3.00mm
Plating min - Mating	5.080μm
Plating min - Termination	5.080μm
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole - Compliant Pin
Electrical	
Current - Maximum per Contact	8.5A
Voltage - Maximum	600V
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-70873-0314-001
Product Specification	430450001-PS-KO-000, 430450001-PS-SP-000, PS-43045-001
Sales Drawing	SD-44914-002-001
Symbol/Footprint Data	SYM-44914-1801-001
Test Summary	TS-43045-001-001, TS-43045-002-001, TS-46235-001-001