


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0457190004**
Status: **Active**
Overview: Edge Card Connectors
Description: 12.90mm Pitch EXTreme PowerEdge Connector, 2.36mm Thick PC Board, Mates to a 1.57mm Thick Card Edge or Bus Bar Tab

Documents:

3D Model	Packaging Specification PK-45714-001-001 (PDF)
3D Model (PDF)	Test Summary TS-45844-001-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-45719-001-001 (PDF)	



Agency Certification

CSA	LR19980
TUV	R72090228

General

Product Family	Edge Card Connectors
Series	45714
Component Type	Edgecard to PCB
Data Rate	Unrated
Edge Card Thickness	1.57mm
High Power Bay (30.0A or more)	Yes
Orientation	Vertical
Overview	Edge Card Connectors
Product Name	Bus Bar Socket, EXTreme PowerEdge
Standard Based	General
Taxonomy	Card Edge Connectors
UPC	822348678365

Physical

(p)ower-(s)ignal Configuration	4p - 0s
Circuit Size Range	1-64 Circuits
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Durability (mating cycles max)	200
Entry Angle	Vertical (Top Entry)
Flammability	94V-0
Keying to Mating Part	N/A
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	5.200/g
PC Tail Length	3.63mm
PCB Thickness - Recommended	2.40mm
Packaging Type	Tray
Pitch - Mating Interface	12.90mm
Plating min - Mating	0.762µm
Plating min - Termination	3.810µm
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	40.0A
Voltage - Maximum	250V

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

45714 Series

Mates With

1.58mm Double Sided Card Edge or Bus Bar Tab

Solder Process Data

Lead-free Process Capability

N/A

Material Info**Reference - Drawing Numbers**

Packaging Specification

PK-45714-001-001

Product Specification

PS-45719-001-001

Sales Drawing

SD-45719-001-001

Test Summary

TS-45844-001-001

This document was generated on 10/11/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION