

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0039000121](#)  
**Status:** **Active**  
**Overview:** [Mini-Fit Family Power Connectors](#)  
**Description:** [Mini-Fit Male Crimp Terminal, Tin \(Sn\) Plated Brass Contact, 18-24 AWG, Bag](#)

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Application Specification 55560001-AS-000 (PDF)</a>
<a href="#">Product Specification 55560002-PS-CH-000 (PDF)</a>	<a href="#">Packaging Specification PK-5556-003-001 (PDF)</a>
<a href="#">Product Specification 55560002-PS-ES-000 (PDF)</a>	<a href="#">Test Summary 55560010-TS-000 (PDF)</a>
<a href="#">Product Specification 55560002-PS-SK-000 (PDF)</a>	<a href="#">Test Summary TS-5556-002-001 (PDF)</a>
<a href="#">Product Specification PS-5556-001-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-5556-002-001 (PDF)</a>	

**General**

Product Family	Crimp Terminals
Series	<a href="#">5558</a>
Application	Power, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	<a href="#">Mini-Fit Family Power Connectors</a>
Packaging Alternative	<a href="#">39000120 (Reel)</a>
Product Name	Mini-Fit
Taxonomy	Crimp Terminals
UPC	800753512047

**Physical**

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.138/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm <sup>2</sup>	N/A

**Electrical**

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

Engineering Number	5558-SL
--------------------	---------

**Reference - Drawing Numbers**

Application Specification	<a href="#">55560001-AS-000</a>
Packaging Specification	<a href="#">PK-5556-003-001</a>
Product Specification	<a href="#">55560002-PS-CH-000</a> , <a href="#">55560002-PS-ES-000</a> , <a href="#">55560002-PS-SK-000</a> , <a href="#">PS-5556-001-001</a> , <a href="#">PS-5556-002-001</a>
Sales Drawing	<a href="#">SD-5558-XSX-001</a>
Test Summary	<a href="#">55560010-TS-000</a> , <a href="#">TS-5556-002-001</a>



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2022)4187-DC (10  
June 2022)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[5558 Series](#)

**Use With**

Mini-Fit Jr. Plug Housing [5559](#) <br>Mini-Fit  
BMI Plug Housing [42475](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

Extraction Tool for	<a href="#">11030044</a>
Mini-Fit Jr. Terminals	
FineAdjust Applicator	<a href="#">2037026300</a>
for Mini-Fit Double	
Crimp Applications	
Using Two 22 AWG	
Wires	
PremiumGrade Hand	<a href="#">638190901</a>
Crimp Tool for Mini-	
Fit Jr. Male and	

Female Terminals,  
 18-24 AWG  
 FineAdjust 639015600  
 Applicator for 18-20  
 AWG and 18-24  
 AWG Wires with  
 Insulation Diameter  
 1.90-2.30mm  
 FineAdjust Applicator639023900  
 for Insulation OD  
 1.40-1.70mm - 18-24  
 AWG  
 FineAdjust Applicator639024800  
 for Insulation OD  
 2.50-2.95mm  
 Optimized for 18  
 AWG Only  
 FineAdjust Applicator639024900  
 for Insulation OD  
 2.30-2.60mm - 18-24  
 AWG  
 FineAdjust Applicator639047800  
 for Insulation OD  
 2.50-2.95mm, 18-24  
 AWG  
 FineAdjust Applicator639048000  
 for Insulation OD  
 1.65-2.05mm, 18-24  
 AWG  
 T2 Terminator 639115600  
 for insulation OD  
 1.90-2.30mm - 18-24  
 AWG  
 T2 Terminator 639123900  
 for insulation OD  
 1.40-1.70mm - 18-24  
 AWG  
 T2 Terminator 639124800  
 for insulation OD  
 2.50-2.95mm  
 optimized for 18  
 AWG only  
 T2 Terminator 639124900  
 for insulation OD  
 2.30-2.60mm - 18-24  
 AWG  
 T2 Terminator 639147800  
 for Mini-Fit Crimp  
 Terminals, 18-24  
 AWG with Large  
 Insulation ODs  
 T2 Terminator 639148000  
 for Mini-Fit Crimp  
 Terminals, 18-24  
 AWG with Smaller  
 Insulation ODs

This document was generated on 09/26/2022

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**