

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [055909974](#)  
**Status:** **Active**  
**Overview:** SlimStack Board-to-Board/Board-to-FPC Connectors  
**Description:** SlimStack Board-to-Board Plug, 0.40mm Pitch, J-Bend Series, 0.20µm Gold (Au) Plating, 1.50 or 1.80mm Mated Height, 3.40 or 4.20mm Mated Width, 12 Circuits

**Documents:**

|  |   |
|--|---|
| <a href="#">2D Drawing (DXF)</a>                             | <a href="#">Packaging Specification SPK-55909-001-001 (PDF)</a> |
| <a href="#">Drawing (PDF)</a>                                | <a href="#">Datasheet (PDF)</a>                                 |
| <a href="#">2D Drawing DXF (PDF)</a>                         | <a href="#">Product Guide (PDF)</a>                             |
| <a href="#">3D Model</a>                                     | <a href="#">RoHS Certificate of Compliance (PDF)</a>            |
| <a href="#">3D Model (PDF)</a>                               | <a href="#">Reference Guide (PDF)</a>                           |
| <a href="#">Product Specification PS-51338-002-001 (PDF)</a> |   |

**General**

|                |  |
|----------------|--|
| Product Family | PCB Headers  |
| Series         | <a href="#">55909</a>  |
| Application    | Board-to-Board, Signal   |
| Comments       | Solder Tab Plating: Tin  |
| Overview       | <a href="#">SlimStack Board-to-Board/Board-to-FPC Connectors</a> |
| Product Name   | SlimStack  |
| Series Name    | 0.4, J-Bend  |
| Taxonomy       | Board-to-Board Connectors  |
| UPC            | 822348857920   |

**Physical**

|                                |                       |
|--------------------------------|-----------------------|
| Breakaway                      | No                    |
| Circuits (Loaded)              | 12                    |
| Circuits (maximum)             | 12                    |
| Color - Resin                  | Black                 |
| Durability (mating cycles max) | 30                    |
| Glow-Wire Capable              | No                    |
| Lock to Mating Part            | Yes                   |
| Mated Height                   | 1.50mm, 1.80mm        |
| Mated Width                    | 3.40mm, 4.20mm        |
| Material - Metal               | Brass                 |
| Material - Plating Mating      | Gold                  |
| Material - Plating Termination | Gold                  |
| Net Weight                     | 17.630/mg             |
| Number of Rows                 | 2                     |
| Orientation                    | Vertical              |
| PCB Locator                    | No                    |
| PCB Retention                  | Yes                   |
| Packaging Type                 | Embossed Tape on Reel |
| Pitch - Mating Interface       | 0.40mm                |
| Pitch - Termination Interface  | 0.40mm                |
| Temperature Range - Operating  | -40° to +105°C        |
| Termination Interface: Style   | Surface Mount         |


**Electrical**

|                               |                 |
|-------------------------------|-----------------|
| Current - Maximum per Contact | 0.3A            |
| Voltage - Maximum             | 50V AC (RMS)/DC |

**Material Info**

**Reference - Drawing Numbers**

|                         |                   |
|-------------------------|-------------------|
| Packaging Specification | SPK-55909-001-001 |
| Product Specification   | PS-51338-002-001  |



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2022)4187-DC (10  
June 2022)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[55909 Series](#)

**Mates With**

SlimStack J-Bend Receptacle [51338](#)

This document was generated on 10/20/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**