

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0705530003

Status:

Active

Overview:

SL Modular Connectors

Description:

2.54mm Pitch SL Header, Low Profile, Single Row, Right Angle, 3.05mm Pocket, Shrouded, 4 Circuits, 0.38µm Gold (Au) Selective Plating, Tin (Sn) PC Tail Plating

Documents:

3D Model

Drawing (PDF)

Product Specification PS-70400-001 (PDF)

Product Specification PS-70541-001 (PDF)

Packaging Specification PK-70873-0015-001 (PDF)

Test Summary TS-70541-100-001 (PDF)

RoHS Certificate of Compliance (PDF)



Series image - Reference only

Agency Certification		
CSA		LR19980
UL		E29179
General		
Product Family		PCB Headers
Series		70553
Application		Signal, Wire-to-Board
Overview		SL Modular Connectors
Product Name		SL
Taxonomy		PCB Headers and Receptacles
UPC		800753597389

Physical		
Breakaway		No
Circuits (Loaded)		4
Circuits (maximum)		4
Color - Resin		Black
Durability (mating cycles max)		50
Flammability		94V-0
Glow-Wire Capable		No
Guide to Mating Part		Yes
Lock to Mating Part		Yes
Material - Metal		Brass, Phosphor Bronze
Material - Plating Mating		Gold
Material - Plating Termination		Tin
Material - Resin		High Temperature Thermoplastic
Net Weight		0.917/g
Number of Rows		1
Orientation		Right Angle
PC Tail Length		3.30mm
PCB Locator		No
PCB Retention		None
PCB Thickness - Recommended		1.60mm
Packaging Type		Tube
Pitch - Mating Interface		2.54mm
Plating min - Mating		0.381µm
Plating min - Termination		1.905µm
Polarized to Mating Part		Yes
Shrouded		Fully
Stackable		No
Temperature Range - Operating		-40° to +105°C
Termination Interface: Style		Through Hole

Electrical

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

70553 Series

Mates With

SL Crimp Housing 70066 Option N, 70066 Option G, 70430 Option G, 70400 Option G

Current - Maximum per Contact	3.0A
Voltage - Maximum	250V

Solder Process Data

Duration at Max. Process Temperature (seconds)	003
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-70873-0015-001
Product Specification	PS-70400-001, PS-70541-001
Sales Drawing	SDA-70553-XXXX-001
Test Summary	TS-70541-100-001

This document was generated on 10/20/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION