

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0431600105](#)
Status: **Active**
Overview: [Sabre Power Connector](#)
Description: Sabre Vertical Header, 5 Circuits, Glow-Wire Capable, PCB Thickness 1.60mm, without Board Lock

Documents:

Drawing (PDF)	Test Summary 444410000-TS-000 (PDF)
3D Model	Datasheet (PDF)
3D Model (PDF)	Symbol Footprint Data SYM-43160-0105-001 (PDF)
Product Specification PS-44441-9999-001 (PDF)	RoHS Certificate of Compliance (PDF)
Packaging Specification PK-43160-0010-001 (PDF)	

Agency Certification

CSA	LR19980
UL	E29179


General

Product Family	PCB Headers
Series	43160
Application	Power, Wire-to-Board
Comments	Fully Polarized, high power wire-to-board and wire-to-wire connector system; This Molex product is manufactured from material that has the following ratings, tested by independent agencies: a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12 and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options.

Overview	Sabre Power Connector
Product Name	Sabre
Taxonomy	PCB Headers and Receptacles
UPC	800754377591

Physical

Breakaway	No
Circuits (Loaded)	5
Circuits (maximum)	5
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	Yes
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[43160 Series](#)

Mates With

[444412005 Sabre Receptacle Housing](#)

Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	5.718/g
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.81mm
PCB Locator	Yes
PCB Retention	N/A
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	7.50mm
Pitch - Termination Interface	7.50mm
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +75°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	18.0A
Voltage - Maximum	600V

Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-free Process Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-43160-0010-001
Product Specification	PS-44441-9999-001
Sales Drawing	431600001-SD-000
Symbol/Footprint Data	SYM-43160-0105-001
Test Summary	444410000-TS-000

This document was generated on 10/12/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION