

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0857931007](#)

Status: **Active**

Overview: [Magnetic Jacks](#)

Description: MXMag Gigabit Ethernet 8 Core Non-PoE Single-Port RJ45 Connector, 33.02mm Depth, 3.15mm Phy Pin Length, Right-Angle, Inverted Profile, with Shield Tabs, with Green-Yellow/Green LEDs, Standard Temperature, Tray

Documents:

[3D Model \(PDF\)](#)

[3D Model](#)

[Drawing \(PDF\)](#)

[Product Specification PS-85793-001-001 \(PDF\)](#)

[Packaging Specification PK-85759-001-001 \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E177474

General

Product Family	Modular Jacks/Plugs
Series	85793
Component Type	PCB Jack
Depth	33.02mm
Magnetic	Yes
Overview	Magnetic Jacks
Performance Category	1000Mb
Power over Ethernet (PoE)	Non-PoE
Product Name	Magnetic Jack, MXMag, RJ45
Taxonomy	Modular Jacks and Plugs
UPC	884982486546

Physical

Color - Resin	Black
Durability (mating cycles max)	750
Inverted / Top Latch	Yes
Jack Height	13.87mm
Keying to Mating Part	None
Lightpipes/LEDs	LEDs
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	PBT
Net Weight	10.500/g
Orientation	Right Angle (Side Entry)
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Panel Mount	Spring Tabs
Plating min - Mating	0.381µm
Plating min - Termination	1.270µm
Port Configuration	1x1
Positions / Loaded Contacts	8/8
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	0° to +70°C
Termination Interface: Style	Through Hole
Wire/Cable Type	N/A

Electrical



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 7(c)-I

REACH SVHC

Contained Per - D(2022)4187-DC (10 June 2022)
2-Methyl-1-(4-methylthiophenyl)-2-morpholinoprop

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

50 Image

Not Relevant

Not Contained

Search Parts in this Series

[85793 Series](#)

Mates With

Plugs according to IEC 60603-7

Current - Maximum per Contact	1.0A
Grounding to PCB	Yes
Grounding to Panel	Yes
Shielded	Yes
Voltage - Maximum	150V (RMS)

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-85759-001-001
Product Specification	PS-85793-001-001
Sales Drawing	857931001-000

This document was generated on 08/27/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION