

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0461141228

Status:

Active

Overview:

EXTreme LPHPower Connectors

Description:

1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, Compliant Pin, 12 Power Contacts, 28 Signal Contacts, Select Gold (Au) Plating, with BMI Guides

Documents:

3D Model

Application Specification AS-46114-001-001 (PDF)

3D Model (PDF)

Packaging Specification PK-46114-003-001 (PDF)


Drawing (PDF)

Symbol Footprint Data SYM-46114-1228-001 (PDF)

Product Specification PS-46114-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19880
UL	E29179
Application tooling part link	
Application Tooling Part Link	62100-6300
Application Tooling Part Link	62201-8671
General	
Product Family	PCB Receptacles
Series	46114
Application	Board-to-Board, Power
Comments	Press Fit Pin
Overview	EXTreme LPHPower Connectors
Product Name	EXTreme LPHPower
Taxonomy	Board-to-Board Connectors
UPC	800756886398
Physical	
(p)ower-(s)ignal Configuration	12p - 28s
Circuits (Loaded)	30
Circuits (maximum)	30
Color - Resin	Black
Durability (mating cycles max)	250
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	15.202/g
Number of Rows	2
Orientation	Vertical
PCB Locator	No
PCB Retention	None
Packaging Type	Tube
Pitch - Mating Interface	1.27mm, 12.00mm
Pitch - Termination Interface	1.27mm, 2.50mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

46114 Series

Mates With

45985 EXTreme LPHPower Header

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
LPH Vertical Receptacle Power Terminal Removal Tool	621006300
Vertical Receptacle Press-In Tool	622018671

Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole - Compliant Pin
Electrical	
Current - Maximum per Contact	30.0A
Grounding to PCB	No
Voltage - Maximum	250V AC (RMS)/DC
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-46114-001-001
Packaging Specification	PK-46114-003-001
Product Specification	PS-46114-001-001
Sales Drawing	SD-46114-120-001
Symbol/Footprint Data	SYM-46114-1228-001

This document was generated on 10/21/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION