

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0901210126](#)  
**Status:** **Active**  
**Overview:** [C-Grid III Interconnects](#)  
**Description:** 2.54mm Pitch C-Grid III Header, Single Row, Right-Angle, 6 Circuits, Tin (Sn) Plating

**Documents:**

|   |  |
|---|--|
| <a href="#">3D Model</a>                                      | <a href="#">Application Specification 901190001-AS-000 (PDF)</a> |
| <a href="#">Drawing (PDF)</a>                                 | <a href="#">Packaging Specification PK-90120-100-001 (PDF)</a>   |
| <a href="#">Product Specification PS-99020-0001-001 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>             |

**Agency Certification**

UL E29179

**General**


|                |  |
|----------------|--|
| Product Family | PCB Headers                              |
| Series         | <a href="#">90121</a>                    |
| Application    | Signal, Wire-to-Board                    |
| Overview       | <a href="#">C-Grid III Interconnects</a> |
| Product Name   | C-Grid III                               |
| Taxonomy       | PCB Headers and Receptacles              |
| UPC            | 800753714434                             |

**Physical**

|                                |                |
|--------------------------------|----------------|
| Breakaway                      | Yes            |
| Circuits (Loaded)              | 6              |
| Circuits (maximum)             | 6              |
| Color - Resin                  | Black          |
| First Mate / Last Break        | No             |
| Flammability                   | 94V-0          |
| Glow-Wire Capable              | No             |
| Guide to Mating Part           | No             |
| Keying to Mating Part          | None           |
| Lock to Mating Part            | None           |
| Material - Metal               | Brass          |
| Material - Plating Mating      | Tin            |
| Material - Plating Termination | Tin            |
| Material - Resin               | Polyester      |
| Net Weight                     | 0.479/g        |
| Number of Rows                 | 1              |
| Orientation                    | Right Angle    |
| PC Tail Length                 | 2.90mm         |
| PCB Locator                    | No             |
| PCB Retention                  | None           |
| Packaging Type                 | Tray           |
| Pitch - Mating Interface       | 2.54mm         |
| Pitch - Termination Interface  | 2.54mm         |
| Plating min - Mating           | 4.064µm        |
| Plating min - Termination      | 3.048µm        |
| Polarized to Mating Part       | No             |
| Polarized to PCB               | No             |
| Shrouded                       | No             |
| Stackable                      | No             |
| Temperature Range - Operating  | -55° to +125°C |
| Termination Interface: Style   | Through Hole   |

**Electrical**

Current - Maximum per Contact 3.0A



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2022)4187-DC (10  
June 2022)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[90121](#) Series

**Mates With**

C-Grid III Vertical PCB Receptacle [90147](#)  
 . C-Grid III Right-Angle PCB Receptacle  
[90148](#) . C-Grid III Modular Crimp Housing  
[90123](#)

Voltage - Maximum 350V

**Solder Process Data**

Duration at Max. Process Temperature (seconds) 003  
Lead-free Process Capability WAVE  
Max. Cycles at Max. Process Temperature 001  
Process Temperature max. C 235

**Material Info**

**Reference - Drawing Numbers**

Application Specification 901190001-AS-000  
Packaging Specification PK-90120-100-001  
Product Specification PS-99020-0001-001  
Sales Drawing SD-90121-001-001

This document was generated on 10/21/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**