


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0901220133](#)
Status: **Active**
Overview: [C-Grid III Interconnects](#)
Description: 2.54mm Pitch C-Grid III Header, Dual Row, Right-Angle, 26 Circuits, 4µm Tin (Sn) over Nickel (Ni)

Documents:

3D Model	Application Specification 901190001-AS-000 (PDF)
3D Model (PDF)	Packaging Specification PK-90120-100-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-99020-0001-001 (PDF)	



Agency Certification

UL E29179

General

Product Family	PCB Headers
Series	90122
Application	Signal, Wire-to-Board
Overview	C-Grid III Interconnects
Product Name	C-Grid III
Taxonomy	PCB Headers and Receptacles
UPC	800753709867

Physical

Breakaway	Yes
Circuits (Loaded)	26
Circuits (maximum)	26
Color - Resin	Black
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	2.146/g
Number of Rows	2
Orientation	Right Angle
PC Tail Length	2.90mm
PCB Locator	No
PCB Retention	None
Packaging Type	Tray
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	4.064µm
Plating min - Termination	3.048µm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Stackable	No
Temperature Range - Operating	-55° to +125°C
Termination Interface: Style	Through Hole

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[90122](#) Series

Mates With

C-Grid III Vertical PCB Receptacle [90151](#)
 . C-Grid III Right-Angle PCB Receptacle
[90152](#) . C-Grid III Crimp Housing [90142](#) . C-
 Grid III Modular Crimp Housing [90143](#)

Electrical

Current - Maximum per Contact
Voltage - Maximum

3.0A
350V

Solder Process Data

Lead-freeProcess Capability

WAVE

Material Info**Reference - Drawing Numbers**

Application Specification
Packaging Specification
Product Specification
Sales Drawing

901190001-AS-000
PK-90120-100-001
PS-99020-0001-001
SDA-90122-001

This document was generated on 10/18/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION