

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936010292

Status:


Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect Push-in Terminal Insert, Female, 24-Pole, 16A, Numbered 25-48, Silver (Ag) Plated Contacts, Size 24B «104x27»



Series image - Reference only

Documents:

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	256883
UL	E249674
General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Comments	Stranded wire with bush terminal 0.14-2.50 (26-14 AWG), Stranded wires with single strand greater than and equal to 0.20mm (16-12 AWG), and Solid wires 0.50-2.50 (20-14 AWG)
Component Size	24B «104X27»
Component Type	Inserts - Push-in Terminal
Insert Series	S-EP
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977
Taxonomy	Heavy-Duty Connectors
UPC	887191881508
Physical	
Durability (mating cycles max)	500
Flammability	UL 94V-0
Gender	Female
Insert Color	Grey
Material - Contact	Copper Alloy
Material - Insert	Polycarbonate
Material - Plating	Silver
Net Weight	127.000/g
Number of Rows	2
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	24
Stripping Length	9.00-11.00mm
Temperature Range - Operating	-40° to +125°C
Wire Size AWG	12-16, 14-20, 14-26
Wire Size mm²	0.14-2.50, 0.50-2.50, 1.50-4.00
Electrical	
Current - Maximum per Contact	16.0A
Voltage - Maximum	500V
Material Info	
Engineering Number	7324.5866.0

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

93601 Series

Mates With

936010296 Male Pushin Terminal Insert

Use With

Size 24B «104x27» Hoods and Housings

This document was generated on 10/11/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION