

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0755615000](#)
Status: **Active**
Overview: [EXTreme PowerMass High-Current Connectors](#)
Description: EXTreme PowerMass 0.13mm Pitch, 80A per module, Right-Angle Plug, Tail Length 3.07mm, without Pegs

Documents:

3D Model	Product Specification PS-75431-999-001 (PDF)
Drawing (PDF)	Packaging Specification PK-46081-100-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification


CSA	LR19980
UL	E29179

General

Product Family	PCB Headers
Series	75561
Application	Board-to-Board, Power
Comments	80A per module, 40A per contact (2 contacts per module)
Overview	EXTreme PowerMass High-Current Connectors
Product Name	EXTreme PowerMass
Taxonomy	Board-to-Board Connectors
UPC	800756716268

Physical

(p)ower-(s)ignal Configuration	2p - 0s
Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4
Durability (mating cycles max)	50
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	No
Material - Metal	Copper-Nickel-Silicon
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	11.218/g
Number of Rows	2
Orientation	Right Angle
PC Tail Length	3.07mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	2.40mm
Packaging Type	Tray
Pitch - Mating Interface	3.00mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Closed Ends
Stackable	No
Surface Mount Compatible (SMC)	Yes



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[75561](#) Series

Mates With

[755455000](#) EXTreme PowerMass Receptacle, [755455001](#) EXTreme PowerMass Receptacle

Temperature Range - Operating -40° to +105°C
Termination Interface: Style Through Hole

Electrical

Current - Maximum per Contact 40.0A
Voltage - Maximum 450V

Material Info

Reference - Drawing Numbers

Packaging Specification PK-46081-100-001
Product Specification PS-75431-999-001
Sales Drawing SD-75561-100-001

This document was generated on 10/20/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION