

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1053252004](#)
Status: **Active**
Overview: Nano-Fit Power Connectors
Description: Nano-Fit Terminal Position Assurance (TPA) Retainer, 2.50mm Pitch, 4 Circuits, Natural

Documents:

3D Model	Packaging Specification PK-105325-100-000 (PDF)
Drawing (PDF)	Test Summary 1053000000-TS-000 (PDF)
3D Model (PDF)	Datasheet (PDF)
Product Specification PS-105300-100-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-105300-100-001 (PDF)	

General

Product Family	Accessories
Series	105325
Comments	Operating temperature is -40° to +105° for tin and -40° to +115° for gold
Component Type	Terminal Position Assurance
Overview	Nano-Fit Power Connectors
Product Name	Nano-Fit
Taxonomy	Connector Accessories
UPC	889056029148

Physical

Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Natural
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.120/g
Number of Rows	1
Packaging Type	Bag
Temperature Range - Operating	-40° to +105°C, -40° to +115°C

Material Info

Reference - Drawing Numbers

Application Specification	AS-105300-100-001
Packaging Specification	PK-105325-100-000
Product Specification	PS-105300-100-001
Sales Drawing	SD-105325-100-000
Test Summary	1053000000-TS-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[105325 Series](#)

Use With

Nano-Fit TPA Receptacle Housing [105307](#)
, [105308](#)
 Nano-Fit TPA Plug Housings
[200277](#) , [201444](#)