


 Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri

 Active

Always EU RoHS/ELV Compliant (Statement of Compliance)

- ? Receptacle
- ? HV-100
- ? Number of Positions = 10
- ? Number of Rows = Dual
- ? Standard Profile

[View all Features](#) | [Find Similar Products](#)

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

Product Drawings:

[HV 100 BUCHSENSTECKER ZWEIREIHIG \(GEDICHTETE VERSION\)](#)
(PDF, German)

? None Available

? None Available

? None Available

? None Available

- ? 2D Drawing (DXF, Version C1)
- ? 3D Model (IGES, Version C1)
- ? 3D Model (STEP, Version C1)

List all Documents

? Product Line Information

? Tooling

Product Type Features:

? Product Type = Receptacle
 ? Connector Series = HV -100
 ? Number of Positions = 10
 ? Profile = Standard
 ? Mount Angle = Vertical
 ? Mounting Pattern (mm [in]) = 2.54 x 2.54 [.100
 x .100]
 ? Sealed = Yes
 ? Holdddown Feature = Without
 ? PCB Retention Feature = Yes
 ? Closed Entry = With
 ? Board Standoff = With

? Stackable = Yes

? Termination Method = Through Hole
? Termination (Solder) Post Length (mm [in]) = 3.10 [0.122]
? Solder Tail Contact Plating = Tin

? Number of Rows = Dual
 ? Connector Height (mm [in]) = 7.00 [0.276]
 ? Centerline, Matrix (mm [in]) = 2.54 [.100]
 ? PCB Retention Method = Retention Solder Tails
 ? Closed Bottom = Without

? Contact Mating Area Plating Material = Gold
(30)

? Contact Material = Phosphor Bronze

? Housing Entry Style = Top
 ? Housing Material = Polyester GV
 ? Housing Flammability Rating = UL 94V -0
 ? Housing Color = Green

- ? Government/Industry Qualification = No
- ? RoHS/ELV Compliance = RoHS compliant, ELV compliant
- ? Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

? Brand = AMP