


TE CONNECTIVITY (TE) RESERVES THE RIGHT TO CHANGE THIS DRAWING AT ANYTIME. USERS SHOULD EVALUATE THE SUITABILITY OF THE PRODUCT FOR THEIR APPLICATION.	REVISION			
	LTR	DESCRIPTION	DATE	APPROVED
	H	REVISED PER ECO-14-015963	10/24/2014	I. MYONG
	J	REVISED PER ECO-15-002435	02/18/2015	H. SMITH



CODE 18 – TINEL-LOCK ADAPTER – STRAIGHT

NOTES:

- THIS PRODUCT IS DESIGNED TO TERMINATE A BRAIDED CABLE SHIELD AND A HEAT SHRINKABLE LIPPED BOOT TO A CONNECTOR.
- SEE CH00-0250-008 FOR ORDERING INFORMATION, MODIFICATIONS AND ADDITIONAL DIMENSIONS.
- SEE DRAWING "TR" FOR DETAIL ON TINEL-LOCK RING. RINGS ARE DESIGNED TO BE HEATED ELECTRICALLY. ALL RINGS ARE MARKED WITH THERMOCHROMIC PAINT WHICH CHANGES COLOR WHEN INSTALLATION TEMPERATURE IS REACHED.
- ADAPTER TO BE PERMANENTLY MARKED WITH CODE IDENT. NO. AND PART NO. LESS RING DESIGNATOR (E.G., 06090-TXR18AB00-1406 YYWW). RINGS SHALL BEAR NO MARKING.
- FOR LARGER ENTRY SIZES, A 2 PIECE ADAPTER (TYPE II) IS SUPPLIED.
- ADAPTER MATES TO MIL-C-5015D, CLASS A, E & R, MS3100, MS3101 & MS3106. RESILIENT INSERT, SOLDER TYPE & BENDIX 10-214, CANNON CA-RX COMMERCIAL CRIMP TYPE.
- ADDITIONAL PIECE(S) SUPPLIED WHEN CONNECTOR MANUFACTURER IS UNKNOWN ("D" IN TABLE III) AND ENTRY SIZE DOES NOT EXCEED VALUE IN TABLE I. SEE FIGURE A PAGE 2 OF 4.
- ALL THREAD SIZES FOR ORDER NO. APPLY.
- ANTI-ROTATIONAL SET SCREW, 3 THREADED HOLES 120°±5° APART, SINGLE MATING SET SCREW SUPPLIED: AN565DC4H2. NOT REQUIRED FOR TYPE II ADAPTERS.
- THESE DIMENSIONS APPLY IF ADAPTER MATERIAL IS STAINLESS STEEL.








If this document is printed it becomes uncontrolled. Check for the latest revision

©2015 TE CONNECTIVITY LTD. FAMILY OF COMPANIES. ALL RIGHTS RESERVED
 TE CONNECTIVITY AND TE CONNECTIVITY (LOGO) ARE TRADEMARKS.
 OTHER LOGOS PRODUCT AND/OR COMPANY NAMES MAY BE TRADEMARKS OF THEIR RESPECTIVE OWNERS.

Raychem Adapters
 CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. REFERENCE METRIC DIMENSIONS ARE IN BRACKETS [metric].		DRAWN: T. NGUYEN	DATE: 02/21/2014	 TE Connectivity				
		CHECKED: I. MYONG	DATE: 02/24/2014					
		APPROVED: I. MYONG	DATE: 02/25/2014	TITLE: CODE 18 – TINEL-LOCK ADAPTER				
		MATERIAL: SEE NOTES	FINISH: SEE NOTES					
DECIMALS TOLERANCES: XXX ± .005 [0.13mm] XX ± .01 [0.25mm] X ± .1 [0.50mm] ANGLES TOLERANCE: ± 1°		CAD FILE: TXR18.dwg	THIRD ANGLE PROJECTION: 	SIZE: A	SHEET: 1 OF 4	CAGE CODE: 06090	DRAWING NO: TXR18	REV. J
SCALE: DO NOT SCALE THIS DRAWING								

SCALE:
DO NOT SCALE THIS DRAWING



If this document is printed it becomes uncontrolled. Check for the latest revision

Raychem Adapters CUSTOMER DRAWING



DO NOT
SCALE THIS
DRAWING

SIZE
A

CAGE
06090

SHEET
2 OF 4

DWG. NO.

TXR18

REV
J

TABLE I

ORDER NO.	SHELL SIZE —	MFR CODE TABLE III	MAX ENTRY SIZE TYPE I	A THREAD CLASS 2B	B DIA MAX	C MAX	D MAX	E MAX	W MAX	E MAX $\triangle_{10}$	W MAX $\triangle_{10}$
08	8S	B	04	.375–32 UNEF	.73 [18.5]	.80 [20.3]	.92 [23.4]	1.23 [31.2]		.93 [23.6]	.93 [23.6]
		C		.438–28 UNEF							
		A,R		.438–27 UNS							
		D		—							
10	10S	—	06	.500–28 UNEF	.79 [20.1]	.83 [21.1]	.95 [24.1]	1.23 [31.2]	1.06 [26.8]	1.25 [31.7]	1.06 [26.8]
11	10SL	C	07	.562–24 UNEF	.85 [21.6]	.83 [21.1]	.95 [24.1]	1.23 [31.2]	1.12 [28.4]	1.32 [33.5]	1.12 [28.4]
		A,B,R		.625–24 UNEF	.92 [23.4]				1.18 [30.0]		1.18 [30.0]
		D		—	—				—		—
12	12 & 12S	B,C	08	.625–24 UNEF	.92 [23.4]	.83 [21.1]	.95 [24.1]	1.23 [31.2]	1.18 [30.0]	1.32 [33.5]	1.18 [30.0]
		A,R		.688–24 UNEF	.98 [24.9]				1.24 [31.6]		1.24 [31.6]
		D		—	—				—		—
14	14 & 14S	—	10	.750–20 UNEF	1.04 [26.4]	.86 [21.8]	.98 [24.9]	1.30 [33.0]	1.31 [33.2]	1.39 [35.4]	1.31 [33.2]
16	16 & 16S	—	12	.875–20 UNEF	1.23 [31.2]	.89 [22.6]	1.02 [25.9]	1.42 [36.1]	1.43 [36.3]	1.42 [36.1]	1.43 [36.3]
18	18	—	12	1.000–20 UNEF	1.35 [34.3]	.92 [23.4]	1.05 [26.7]	1.48 [37.6]	1.49 [37.9]	1.48 [37.7]	1.49 [37.9]
20	20	A,B,C	16	1.125–18 UNEF	1.48 [37.6]	.95 [24.1]	1.08 [27.4]	1.55 [39.4]	1.68 [42.7]	1.55 [39.4]	1.68 [42.7]
		R		1.125–24 UNS							
		D		—							
22	22	—	18	1.250–18 UNEF	1.60 [40.6]	.98 [24.9]	1.11 [28.2]	1.61 [40.9]	1.81 [45.9]	1.61 [40.9]	1.81 [45.9]
24	24	—	20	1.375–18 UNEF	1.73 [43.9]	.98 [24.9]	1.11 [28.2]	1.67 [42.4]	1.93 [49.0]	1.79 [45.4]	1.93 [49.0]
28	28	—	22	1.625–18 UNEF	2.10 [53.3]	1.08 [27.4]	1.17 [29.7]	1.86 [47.2]	2.06 [52.2]	1.86 [47.2]	2.06 [52.2]
32	32	B,C	24	1.875–16 UN	2.23 [56.6]	1.11 [28.2]	1.23 [31.2]	1.92 [48.8]	2.32 [58.9]	2.04 [51.8]	2.31 [58.6]
		A,R		1.906–18 UN							
		D		—							
36	36	B	24	2.062–16 UNS	2.48 [63.0]	1.23 [31.2]	1.27 [32.3]	2.05 [52.1]	2.68 [68.2]	2.16 [54.8]	2.67 [67.7]
		R		2.062–20 UNS							
		C		2.125–16 UN							
		A		2.125–18 UNS							
		D		—							
40	40	B	24	2.312–16 UNS	2.73 [69.3]	1.27 [32.3]	1.30 [33.0]	2.17 [55.1]	2.86 [72.7]	2.28 [58.0]	2.84 [72.2]
		A,C,R		2.375–16 UN							
		D		—							
44	44	—	24	2.625–16 UN	3.23 [82.0]	1.34 [34.0]	1.36 [34.5]	2.42 [61.5]	3.06 [77.6]	2.42 [61.5]	3.06 [77.6]
48	48	C	24	2.812–18 UNS	3.23 [82.0]	1.34 [34.0]	1.53 [39.0]	2.42 [61.5]	3.31 [84.0]	2.42 [61.5]	3.31 [84.0]
		A,R		2.875–16 UN							
		D		—							

If this document is printed it becomes uncontrolled. Check for the latest revision

Raychem Adapters
CUSTOMER DRAWINGDO NOT
SCALE THIS
DRAWINGSIZE
ACAGE
06090SHEET
3 OF 4

DWG. NO.

TXR18

REV
J

TABLE II								
ENTRY SIZE	Z +.010 -.020	S DIA	Y ±.015 [±0.38]	F MAX	G MAX	J MAX	H MAX	K MAX
04	.250 [6.35]	.376 .370 [9.56 9.39]	.550 [13.97]	N/A	N/A	N/A	N/A	N/A
05	.312 [7.92]	.438 .432 [11.13 10.97]	.612 [15.54]	.77 [19.6]	1.10 [28.0]	1.16 [29.5]	1.19 [30.2]	.82 [21.0]
06	.375 [9.52]	.501 .495 [12.73 12.57]	.675 [17.14]	.77 [19.6]	1.10 [28.0]	1.16 [29.5]	1.19 [30.2]	.82 [21.0]
07	.437 [11.09]	.563 .556 [14.31 14.12]	.737 [18.71]	.80 [20.3]	1.10 [28.0]	1.22 [31.0]	1.38 [35.1]	.92 [23.4]
08	.500 [12.70]	.626 .619 [15.91 15.72]	.800 [20.32]	.80 [20.3]	1.12 [28.5]	1.22 [31.0]	1.38 [35.1]	.96 [24.5]
10	.625 [15.87]	.752 .742 [19.11 18.84]	.925 [23.49]	.84 [21.3]	1.16 [29.5]	1.35 [34.3]	1.51 [38.4]	1.18 [30.0]
12	.750 [19.05]	.877 .867 [22.28 22.02]	1.050 [26.67]	.86 [21.8]	1.19 [30.2]	1.40 [35.6]	1.63 [41.4]	1.35 [34.3]
14	.875 [22.23]	1.002 .991 [25.46 25.17]	1.175 [29.84]	.88 [22.4]	1.22 [31.0]	1.46 [37.1]	1.78 [45.2]	1.41 [35.8]
16	1.000 [25.40]	1.127 1.116 [28.63 28.34]	1.300 [33.02]	.91 [23.1]	1.23 [31.4]	1.53 [38.9]	1.88 [47.8]	1.60 [40.6]
18	1.125 [28.57]	1.252 1.241 [31.81 31.52]	1.425 [36.19]	.93 [23.6]	1.24 [31.6]	1.59 [40.4]	2.01 [51.1]	1.66 [42.2]
20	1.250 [31.75]	1.377 1.366 [34.98 34.69]	1.550 [39.37]	.98 [24.9]	1.28 [32.6]	1.78 [45.2]	2.13 [54.1]	2.04 [51.8]
22	1.375 [34.93]	1.502 1.488 [38.15 37.79]	1.675 [42.55]	1.03 [26.2]	1.40 [35.8]	1.85 [47.0]	2.29 [58.2]	2.23 [56.6]
24	1.500 [38.10]	1.627 1.613 [41.33 40.97]	1.800 [45.72]	1.08 [27.4]	1.52 [38.6]	1.92 [48.8]	2.42 [61.5]	2.23 [56.6]

TABLE III	
MFR CODE	CONNECTOR MANUFACTURER (MS 3100, MS 3101 & MS 3106)
A	AMPHENOL—CLASS A
B	BENDIX—CLASS A, E & R
C	CANNON—CLASS A, E & R
D	MFR UNKNOWN, CLASS A, E & R
R	AMPHENOL—CLASS R
—	MFR CODE NOT REQUIRED

If this document is printed it becomes uncontrolled. Check for the latest revision

Raychem Adapters
CUSTOMER DRAWING

	DO NOT SCALE THIS DRAWING	SIZE	CAGE	SHEET	DWG. NO.	REV
		A	06090	4 OF 4	TXR18	J