

## 1393275-6 Product Details



**1393275-6**

TE Part Number: 1393275-6

 [Active](#)

 [Add to Part List](#)

### Automotive Relays

 [Converted to EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Nominal Voltage = 12 VDC
- Rated Current @ 85° C = 2 x 15 Amps.
- PCB Relays
- Without Mounting Bracket(s)
- Contact Arrangement = 1 Form U, SPST-NO-DM, 1 N/O Double Make

[View all Features](#) | [Find Similar Products](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- None Available

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Product Designation = PCB Relays
- Product Type = Power Relay K-D

#### Electrical Characteristics:

- Nominal Voltage (VDC) = 12
- Rated Current @ 85° C (Amps.) = 2 x 15
- [Coil Resistance \(Ω\)](#) = 64
- Switching Current Min. (mA) = 1000
- Switching Voltage Max. (VDC) = See Load Limit Curve
- Switching Voltage Min. (mV) = 5000
- Coil Power, Nominal (W) = 2.25

#### Termination Related Features:

- Height (mm [in]) = 18.50 [0.728]

#### Body Related Features:

- Mounting Bracket(s) = Without
- [Series](#) = V23033
- Length (mm [in]) = 28.00 [1.102]
- Width (mm [in]) = 19.00 [0.748]
- Weight (g [oz]) = 20.00 [0.706]

#### Contact Related Features:

- Contact Material = Silver Based
- Contact Type = Double Make Contact on Armature

#### Housing Related Features:

- Enclosures (Sealing) Type = Open
- Number of Contacts = 2

#### Configuration Related Features:

- [Contact Arrangement](#) = 1 Form U, SPST-NO-DM, 1 N/O Double Make
- [Coil Magnetic System](#) = Monostable

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

#### Operation/Application:

- Application = Cross Carline