



MATED WITH: PASSEND ZU:		LOC	DIST	REVISIONS					
		A1	-	P	LTR	ÄNDERUNGEN DESCRIPTION BESCHREIBUNG	DATE	DWN	APVD
PROJEKT NR.:				A1		Zeichnung erstellt; EG00-0509-99	09.03.99	SR	SM

Maßbild
Outline drawing





AMP PART NO	DESCRIPTION	MATERIAL	SURFACE	PG "X"	PG "Y"	ØA	L
3-7	REDU 42/36.MS	Messing/brass	vernickelt nickel plated	42	36	57	14
2-7	REDU 36/29.MS	Messing/brass	vernickelt nickel plated	36	29	50	12,5
1-7	REDU 29/21.MS	Messing/brass	vernickelt nickel plated	29	21	39	12
0-7	REDU 21/16.MS	Messing/brass	vernickelt nickel plated	21	16	30	10
9-6	REDU 13/11.MS	Messing/brass	vernickelt nickel plated	13.5	11	22	9
8-6	REDU 11/9.MS	Messing/brass	vernickelt nickel plated	11	9	20	8,5
7-6	REDU 42/29.MS	Messing/brass	vernickelt nickel plated	42	29	57	14
6-6	REDU 36/21.MS	Messing/brass	vernickelt nickel plated	36	21	50	12,5
5-6	REDU 29/16.MS	Messing/brass	vernickelt nickel plated	29	16	39	12
4-6	REDU 21/13.MS	Messing/brass	vernickelt nickel plated	21	13,5	30	10
3-6	REDU 16/11.MS	Messing/brass	vernickelt nickel plated	16	11	24	9,5
2-6	REDU 13/9.MS	Messing/brass	vernickelt nickel plated	13.5	9	22	9
1-6	REDU 11/7.MS	Messing/brass	vernickelt nickel plated	11	7	20	8,5
0-6	REDU 16/13.MS	Messing/brass	vernickelt nickel plated	16	13,5	24	9,5

DIMENSIONS: DIMENSIONEN:		DWN	09.03.1999	MATERIAL	FINISH OBERFLÄCHE/FARBE
mm		Schneider		-	-
TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN		CHK	09.03.1999	HTS Elektrotechnik 53819 Neunkirchen, Germany	
n. ISO 8015		APVD	-		
n. ISO 2768 - mH -E		PRODUCT SPEC PRODUKTSPEZ.	-		
n. DIN 16901 - 140		APPLICATION SPEC VERARBEITUNGSSPEZ.	-		
0 PLC		WEIGHT GEWICHT	-		
ANGLES /WINKEL		CUSTOMER DRAWING		NAME REDU reducing piece REDU-Reduzierung rund SIZE A4 CAGE CODE 00779 DRAWING NO ZEICHNUNGS-NR. C=1106060 RESTRICTED TO NUR FÜR	